

NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL SPECIFICATIONS:





BODY AND CONTACT: BERYLLIUM COPPER
INSULATOR: PTFE
RETAINING RING AND COVER: BRASS

2. FINISH SPECIFICATIONS:


CONTACT: .000030 MIN. GOLD OVER .000050 MIN. NICKEL OVER .000050 MIN. COPPER
ALL OTHER METAL PARTS: .000003 MIN. GOLD OVER .000050 MIN. NICKEL OVER .000050 MIN. COPPER

3. COVER SHIPPED LOOSE.

REV	DESCRIPTION	BY DATE	APPD
A	ER057283	ST/2010 lr	SW



CATALOG P/N: 2021D504-405

PER ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [MM] TOLERANCES: DECIMAL: .XX [XX] ± .01 [0.3] XXX [XXX] ± .005 [0.13] XXXX [XXXX] ± .000X ANGLES: ± 2° SCALE: 12:1				 by WINCHESTER Winchester Electronics Corporation 199 Park Road Ext Suite 104 Middlebury, Connecticut 06762			
CUSTOMER SALES DRAWING				SMP RA DIRECT SOLDER PLUG			
DRAWN J	DATE 03/16/2015	APPROVED SM	DATE 04/15/2015				
APPROVED XXX	DATE XX/XX/XX	APPROVED XXX	DATE XX/XX/XX	A	SD2021D504-405	SHT 1	OF 1