

Datasheet

D-Sub 9 Connector with CAN Termination

Bus Termination for High-Speed CAN Systems, according to ISO 11898-2



Order number	1.04.0075.03000
Connector	D-Sub 9, male to female
Bus termination	120 Ohm
Resistor	Between pin 2 and pin 7
Pin allocation	1-to-1
Insulator	PBT glass fibre reinforced
Contact	Brass
Contact plating	Gold plated over nickel
Shell	Tin plated shell
Current rating	3 A
Dielectric strength	500 V AC for 1 minute
Insulator resistance	500 MOhm min. at 500 V DC
Temperature range	-55 °C to 105 °C
Screw	UNC #4-40

Dimensions

All dimensions are in mm.

