




NOTES:

1. MATERIALS:

HANDLE - THERMOPLASTIC, BLACK
CABLE CLAMP - THERMOPLASTIC, BLACK
FLEX RELIEF - THERMOPLASTIC ELASTOMER
BUSHING - THERMOPLASTIC, BLACK

POWER JACK:


HOUSING - COPPER ALLOY, NICKEL PLATED
INSULATOR HOUSING - THERMOPLASTIC, BLACK
TERMINAL INSULATORS - PHENOLIC
PIN, SPRING, TERMINALS - COPPER ALLOY, SILVER PLATED

2. THESE PARTS ARE CURRENT CARRY ONLY NOT TO BE USED FOR CONNECT OR DISCONNECT UNDER LOAD.

3. SHIPPED UNASSEMBLED.

4. THESE PRODUCTS ARE RoHS COMPLIANT

	PART NUMBER	FLEX RELIEF	CABLE RANGE
B	712AC	NONE	Ø 0.324 [8.23]
	712ACF	YES	Ø 0.190 [4.83] - Ø 0.220 [5.59]
	712ACFL	YES	Ø 0.220 [5.59] - Ø 0.250 [6.35]
B	722AC	NONE	Ø 0.324 [8.23]
	722ACF	YES	Ø 0.190 [4.83] - Ø 0.220 [5.59]
	722ACFL	YES	Ø 0.220 [5.59] - Ø 0.250 [6.35]
B	732AC	NONE	Ø 0.324 [8.23]
	732ACF	YES	Ø 0.190 [4.83] - Ø 0.220 [5.59]
	732ACFL	YES	Ø 0.220 [5.59] - Ø 0.250 [6.35]



JACK TERMINAL LAYOUT
SCALE 3:1

						THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.											
					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	SIZE	WIDTH		MULT	LBS/M		TEMPER					
						FINISH SPEC No.				MATERIAL SPEC No.							
						FIRST USED ON			SCALE 3:2			Switchcraft® SHEET 1 OF 1					
B	28009	3-14-18	PC	TJK		DATE DRAWN 12-28-16	BY SRC	CHKD SRC 8-10-17	APVD TJK 8-17-17								
A	ECO 27926	8-17-17	SRC	TJK													
REV	ECO NUMBER	DATE	BY	APVD													
REVISIONS																	
					DO NOT SCALE DRAWING	CABLE POWER JACKS, RoHS											
													PART No.	712AC-732AC 712ACF-732ACF 712ACFL-732ACFL			REV B