





LOC		DIST		REVISIONS			
AF		50		P	LTR	DESCRIPTION	DATE
				A4		REVISED PER ECR-12-013219	08JAN13

- 1 BUDGET FLAG FASTON TERMINALS, BASE P/N 63559, ARE USED IN THIS PRODUCT.
- 2 WIRE SIZE [#18-#14] AWG.
- 3 INSULATION RANGE IS 2.79-4.06 [.110-.160] DIA.
- 4 ALTERNATIVE HOUSING FORM
- 5 PRE-PRODUCTION - FASR REQUIRED.
- 6 GLOW WIRE APPROVED; CONTACT TE ENGINEERING FOR SPECIFICATION (ALL WALL THICKNESSES ARE BETWEEN 0.4-3.0[.015-.118])

SECTION A-A

SECTION B-B



STANDARD	V2 NYLON/NATURAL (WHITE)	TIN PLATE - BRASS	1969109-2
	V2 NYLON/NATURAL (WHITE)	PLAIN - BRASS	
PACKAGING	HOUSING MATERIAL / COLOR	TERMINAL FINISH - MATERIAL	PART NO
THIS DRAWING IS A CONTROLLED DOCUMENT.		TE Connectivity	
DIMENSIONS: mm [INCHES]		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		ASSEMBLY, RECEPTACLE, FLAG, ULTRA-POD, 6.35 [.250] SERIES	
0 PLC ± -		SIZE	RESTRICTED TO
1 PLC ± -		CAGE CODE	A2 00779
2 PLC ± -		DRAWING NO	
3 PLC ± 0.25 [.010]		SCALE	1 OF 1
4 PLC ± -		REV	A4
ANGLES ± -		CUSTOMER DRAWING	
FINISH		SHEET	
SEE TABLE		REV	