

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
GW	-	-	-	SEE SHEET 1	-	-

Cross reference table						
Old part number	Tyco part number	Description	Material	Plating	Cable type	
V23612-A811-G76A	1-1393757-7	Outer conductor	Brass	1 µm Au min in contact area	02Y (sT) CY 0.45/2.0	
		Center conductor	CuBe	1 µm Au min in contact area		
		Dielectric	PEEK/PC	-		
V23612-A811-G76	1-1393757-6	Outer conductor	Brass	1 µm Au min in contact area	02Y (sT) CY 0.45/2.0	
		Center conductor	CuBe	1 µm Au min in contact area		
		Dielectric	PEEK/PC	-		
V23612-A811-A24A	1-1393757-5	Outer conductor	Brass	1 µm Au min in contact area	R1-T 2.0 LI-75 k TZC 75025-315/1.95 FH/HF	
		Center conductor	CuBe	1 µm Au min in contact area		
		Dielectric	PEEK/PC	-		
V23612-A811-A24	1-1393757-4	Outer conductor	Brass	1 µm Au min in contact area	R1-T 2.0 LI-75 k TZC 75025-315/1.95 FH/HF	
		Center conductor	CuBe	1 µm Au min in contact area		
		Dielectric	PEEK/PC	-		

6

OBSOLETE

6

OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm

MATERIAL -

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH -

DWN B. Lenvain 29MAR2001
CHK K. Mattheeuws 09APR2001
APVD R. Leeman 09APR2001
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

tyco
Electronics

Tyco Electronics
Oostkamp - Belgium

NAME
Right angled cable jack
1.6/5.6
with IDC connection

SIZE A3
CAGE CODE 00779
DRAWING NO ©-1393757-16
RESTRICTED TO -

CUSTOMER DRAWING

SCALE 5/1

SHEET 2 OF 2

REV A1

AMP 1470-19 REV 31MAR2000