



REV	DESCRIPTION\PER REQUEST	DRAWN	DATE



VSWR:1.5 Max.
 Per Mil-STD /94
 RoHS Compliant
 50 OHM Impedance
 Operation temperature:-40 to 65 C



RECOMMENDED MOUNTING HOLE



PCB MOUNTING HOLES



5	INSULATOR	1	PTFE	NATURAL	PART NO. 1261A514FSMA	* MAJOR DIMENSION UNLESS OTHERWISE NOTED TOLERANCES 0.5-6=±0.2 6-30=±0.4 30-120=±0.6 120-315=±1.0 ANGLES=±5°				Bomar Interconnect Products,Inc		
4	INSULATOR	1	PTFE	NATURAL								
3	PIN	1	PH0S. BRONZE	GOLD								
2	BODY	1	BRASS	NICKEL	APPROVED	DATE	10/30/14	TITLE SMA R/A P.C. BOARD MOUNT JACK				
1	BODY	1	BRASS	NICKEL	CHECKED	DATE	10/30/14					
NO	DESCRIPTION/DRAWING NO.	Q'TY	MATERIAL	FINISH	DRAWN	DATE	10/30/14					
					Kdi	SCALE	3/1	UNIT	mm	FILE NO. W:\P\AS\ASSMA\ASSMA-10479-TGN Winchester-->20141030		