





ORDERING INFORMATION

8614-00-XX-X-LO-X-XXX-XX

SERIES

OPEN MALE HEADER

NO. OF CONTACTS

01 TO 36 FOR SINGLE ROW
02 TO 72 FOR DOUBLE ROW

NO. OF ROWS.

1-SINGLE ROW
2-DOUBLE ROW

LF : -LEAD FREE

SPECIAL CODE

PLATING : NOTE 2

LO - RIGHT ANGLE SOLDER

Notes:

1. THE PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
2. FOR PLATING DETAILS AND TECHNICAL SPECIFICATION REFER DRAWING C-8614-0000

07	8614-00-XX-X-LO-X-326	4.5	5.7	5.1
06	8614-00-XX-X-LO-X-327	4.6	5.8	3.4
05	8614-00-XX-X-LO-X-328	5.5	6.7	3.2
04	8614-00-XX-X-LO-X-329	5.8	7.0	2.9
03	8614-00-XX-X-LO-X-330	4.5	5.8	2.9
02	8614-00-XX-X-LO-X-331	7.3	8.5	2.5
01	8614-00-XX-X-LO-X-332	4.5	5.7	2.5
Sl. No.	OEN PART NO:	T Y±0.3 Z±0.3		
		DIMENSIONS		

mat'l. code				surface		tolerance		projection	product family		
NOTE 2				ISO 1302 ✓		ISO 406 ISO 1101			8614		
ltr	ecn no	dr	date	tolerances unless otherwise specified				 MM	title		
C	I06-0129	AB	2006-07-24	angles	linear	0.0±0.3			8614 OPEN HEADER (ANGLED SPILL)		
D	I08-0006	MINI	2008-01-17			0.0±0.1					
E	I09-0263	GT	2009-11-17	0°±1°				scale	—		
F	I10-0136	GT	2010-06-23	dr	MINI K VANDANATH	2003-06-15					
G	ELX-L-16699	GM	2014-01-09	enr	GEORGE.V JOSEPH	2003-06-15			dwg no		
				chr	GREGAR.MATHEW	2014-01-09			sheet 1 of 1		
				appd	BIJU K P	2014-01-09			size		
									A3		
sheet index		revision sheet		G					C-8614-0128		
				1					type Product Customer Drawing		