







- NOTES: (b)
- INSULATORS: PBT GF UL 94 V-0; GREY
 - CONTACTS: COPPER ALLOY; PLATING (SEE PART-NO.):
 - PLEASE ADD C for GOLD over NICKEL; 500 MATING CYCLES
 - PLEASE ADD B for GOLD over NICKEL; 400 MATING CYCLES
 - PLEASE ADD A for GOLD over NICKEL; 50 MATING CYCLES
 - CONNECTOR IS PART MARKED: [121□10859X CONEC ABC] (see note 2)

P.C.B. HOLE DRILLINGS



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

					date	name
				drawn	28.05.2015	Heinrich
				appd.	29.05.2015	Lehmenkühler
				norm	DIN EN 60603-2	
				d-old		
5 x b	Ä5665	28.05.15	M.H.	CONEC®		
a	Original					
rev.	description	date	name			

tolerance



dim. in mm

scale: 2:1

material: SEE NOTES

title: MALE CONNECTOR TYPE "E"
48pos. ANGLED
contact spacing 5.08mm

dwg no: 12K1A249

DIN-A3
sh: 1

part no: 121□10859X (see note 2)

RoHS compliant

b

RoHS compliant

(b)

(b)