

SIGN	DATE	DESCRIPTION	APPROVER
△	02/08'07	Part No. is changed.	Aaron
△	06/10'09	The wire strip length changed from 6~7mm to 7~8mm.	Kind
△	06/10'09	The Operating tem. changed from -30°C~105°C to -40°C~115°C	Kind
△	06/10'09	Add the toleration table.	Kind
△	11/21'09	The normal grey No. changed from RAL7004/P to RAL7035/D	Kind
△	03/13'10	Add the 2P mark and Wire strip length is changed	RUNNER

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item 1 Terminal body:Thermoplastic (UL94V-0)
- Item 2 Terminal body:Thermoplastic (UL94V-0)
- Item 3 Terminal lever:Thermoplastic (UL94V-0)
- Item 4 Wire guard:Stainless Steel
- Item 5 Female contact :PhBz (CuSn) Tin plated



Electrical cULus

- Voltage rating: 300V
- Current rating: 10A
- Solid wire(AWG):12-26
- Stranded wire(AWG):12-26
- △ Wire strip length:8-9mm
- Withstanding Voltage:1.6KV
- △ Operating temperature:-40°C to +115°C
- Safety Approval:





PART NO.

HW xx 50 x 0 xxxx G △			RoHS Pb<40,000ppm
Poles	Color	0000 Standard @ Logo	
02 2 CONTACTS	0 Black	000A Standard ANY Logo	
03 3 CONTACTS	5 Green	Any special item by	
... ..	(RAL 6018/T)	customer request,	
24 24 CONTACTS	6 Blue	please contact sales	
	△ 8 Grey	department.	
	(RAL 7035/D)		



2P mark



POLE		2	3	4	5	6	7	8	9	10	11	12
A		10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96
B		5.08	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88
Tol.	±0.15						±0.25					
POLE	13	14	15	16	17	18	19	20	21	22	23	24
A	66.04	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	121.92
B	60.96	66.04	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84
Tol.	±0.30						±0.40					

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HW-5.08 Series Contact on down side									
PART NO.	HWxx50x0xxxxG				DWG NO.	8HW0001					
APPROVED	CHECKED	DESIGNED	DRAWN		CUST NO.	Tolerance					
		Runner 2010.04.06	Kind 2009.06.30			UNIT: mm	X.	±0.50			
						SCALE: NONE	X.X	±0.30			
					SHEET: 01/01	REV: F	X.XX	±0.10			
								X°	±1°		

SHEET: 01/01