

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

PACKAGE 2	108-60121	30u"	45.0	10	44.5	91	70	73.15	89	71.65	164	7-2337939-4	
PACKAGE 1		30u"	86.5	7.0	44.5	91	70	73.15	89	71.65	164	5-2337939-8	
PACKAGE 4		30u"	53.5	7.0	28	58	37	40.15	56	38.65	98	5-2337939-7	
PACKAGE 3		30u"	36.5	7.0	19.5	41	20	23.15	39	21.65	64	5-2337939-6	
NA		30u"	22.5	7.0	12.5	27	6	9.15	25	7.65	36	5-2337939-5	
PACKAGE 1		30u"	10.0	10.0	44.5	91	70	73.15	89	71.65	164	5-2337939-4	
PACKAGE 4		30u"	10.0	10.0	28	58	37	40.15	56	38.65	98	5-2337939-3	
PACKAGE 3		30u"	10.0	10.0	19.5	41	20	23.15	39	21.65	64	5-2337939-2	
NA		30u"	10.0	10.0	12.5	27	6	9.15	25	7.65	36	5-2337939-1	
PACKAGE 1		108-60121-1	15u"	86.5	7.0	44.5	91	70	73.15	89	71.65	164	4-2337939-8
PACKAGE 4	15u"		53.5	7.0	28	58	37	40.15	56	38.65	98	4-2337939-7	
PACKAGE 3	15u"		36.5	7.0	19.5	41	20	23.15	39	21.65	64	4-2337939-6	
NA	15u"		22.5	7.0	12.5	27	6	9.15	25	7.65	36	4-2337939-5	
PACKAGE 1	15u"		10.0	10.0	44.5	91	70	73.15	89	71.65	164	4-2337939-4	
PACKAGE 4	15u"		10.0	10.0	28	58	37	40.15	56	38.65	98	4-2337939-3	
PACKAGE 3	15u"		10.0	10.0	19.5	41	20	23.15	39	21.65	64	4-2337939-2	
NA	15u"		10.0	10.0	12.5	27	6	9.15	25	7.65	36	4-2337939-1	
PACKAGE 1	G/F		86.5	7.0	44.5	91	70	73.15	89	71.65	164	3-2337939-8	
PACKAGE 4	G/F		53.5	7.0	28	58	37	40.15	56	38.65	98	3-2337939-7	
PACKAGE 3	G/F		36.5	7.0	19.5	41	20	23.15	39	21.65	64	3-2337939-6	
NA	G/F		22.5	7.0	12.5	27	6	9.15	25	7.65	36	3-2337939-5	
PACKAGE 1	G/F		10.0	10.0	44.5	91	70	73.15	89	71.65	164	3-2337939-4	
PACKAGE 4	G/F		10.0	10.0	28	58	37	40.15	56	38.65	98	3-2337939-3	
PACKAGE 3	G/F		10.0	10.0	19.5	41	20	23.15	39	21.65	64	3-2337939-2	
NA	G/F		10.0	10.0	12.5	27	6	9.15	25	7.65	36	3-2337939-1	
PACKAGE 2	108-60121		30u"	NA		44.5	91	70	73.15	89	71.65	164	2-2337939-5
PACKAGE 1			30u"	NA		44.5	91	70	73.15	89	71.65	164	2-2337939-4
PACKAGE 4		30u"	NA		28	58	37	40.15	56	38.65	98	2-2337939-3	
PACKAGE 3		30u"	NA		19.5	41	20	23.15	39	21.65	64	2-2337939-2	
NA		30u"	NA		12.5	27	6	9.15	25	7.65	36	2-2337939-1	
PACKAGE 1	108-60121-1	15u"	NA		44.5	91	70	73.15	89	71.65	164	6-2337939-4	
PACKAGE 4		15u"	NA		28	58	37	40.15	56	38.65	98	6-2337939-3	
PACKAGE 3		15u"	NA		19.5	41	20	23.15	39	21.65	64	6-2337939-2	
NA		15u"	NA		12.5	27	6	9.15	25	7.65	36	6-2337939-1	
PACKAGE 1		G/F	NA		44.5	91	70	73.15	89	71.65	164	2337939-4	
PACKAGE 4		G/F	NA		28	58	37	40.15	56	38.65	98	2337939-3	
PACKAGE 3		G/F	NA		19.5	41	20	23.15	39	21.65	64	2337939-2	
NA		G/F	NA		12.5	27	6	9.15	25	7.65	36	2337939-1	
PACKING SPEC	PRODUCT SPEC	GOLD PLATING	W	V	J	D	N	C	B	A	POS.	PART NUMBER	
			MYLAR SIZE (PAGE 4)										

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.3
2 PLC ±0.20
3 PLC ±0.050
4 PLC ±-
ANGLES ±-
FINISH -

MATERIAL

-

-

DWN
FRED LIU
CHK
HOPE LU
APVD
HOPE LU

12JUN2018
12JUN2018
12JUN2018

PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
PCI EXPRESS CARD EDGE CONNECTOR
GEN4 , STANDARD VERSION

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2337939

RESTRICTED TO
-

SCALE
3:1



SHEET
2

OF
6

REV
E

1471-9 (3/13)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

FRONT VIEW

REAR VIEW

36POS AS SHOWN

FRONT VIEW

REAR VIEW

64POS AS SHOWN

FRONT VIEW

REAR VIEW

98POS AS SHOWN

FRONT VIEW

REAR VIEW

164POS AS SHOWN

W

REF

V

REF

J

MYLAR SIZE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.3
2 PLC	±0.20
3 PLC	±0.050
4 PLC	±
ANGLES	±
FINISH	±

MATERIAL

-

-

DWN

FRED LIU

12JUN2018

CHK

HOPE LU

12JUN2018

APVD

HOPE LU

12JUN2018

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME

PCI EXPRESS CARD EDGE CONNECTOR

GEN4 , STANDARD VERSION

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-2337939

-

-

SCALE

3:1

SHEET

4

OF

6

REV

E

1471-9 (3/13)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C


C

B



B

A

A



PACKAGE 1



PACKAGE 2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FRED LIU 12JUN2018	 TE Connectivity								
		CHK HOPE LU 12JUN2018									
DIMENSIONS:		APVD HOPE LU 12JUN2018	NAME PCI EXPRESS CARD EDGE CONNECTOR GEN4 , STANDARD VERSION								
mm		PRODUCT SPEC									
		-	SIZE			CAGE CODE		DRAWING NO		RESTRICTED TO	
		APPLICATION SPEC									
		-									
		-									
MATERIAL		WEIGHT	A200779		C=2337939				-		
-		CUSTOMER DRAWING		SCALE		3:1		SHEET		5 OF 6	
-										REV E	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C


C

B


B

A

A



PACKAGE 3



PACKAGE 4

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
FRED LIU
CHK
HOPE LU
APVD
HOPE LU

12 JUN 2018
12 JUN 2018
12 JUN 2018

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.3
2 PLC ±0.20
3 PLC ±0.050
4 PLC ±-
ANGLES ±-
FINISH

PRODUCT SPEC
APPLICATION SPEC
WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME
PCI EXPRESS CARD EDGE CONNECTOR
GEN4 , STANDARD VERSION

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2337939

RESTRICTED TO
-

SCALE
3:1

SHEET
6 OF 6

REV
E