





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		M4	REVISED PER ECO-20-000170	21MAY2020	KR	JO



SECTION A-A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	19MAR75	TE Connectivity			
DIMENSIONS: INCHES		CHK	20MAR75				
		APVD	20MAR75	NAME			
		PRODUCT SPEC		HOUSING ASSY, LOW PROFILE, EDGE CONNECTOR, FLOW SOLDER, FOR .052 DIA. HOLE,			
TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ± -		—		A2	00779	C=530655	—
1 PLC ± -		—		CUSTOMER DRAWING			
2 PLC ± -		—		SCALE 4:1			
3 PLC ± .005		—		SHEET 1 OF 2			
4 PLC ± -		—		REV M4			
ANGLES ± -		—					
FINISH		—					
SEE CALL-OUT		—					
SEE CALL-OUT		—					

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOCAD

DIST00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

1

.000015 MIN GOLD OVER .000050 MIN. NICKEL IN CONTACT AREA.

2

.000030 MIN GOLD OVER .00005 MIN. NICKEL IN CONTACT AREA.

3

SELECTIVELY LOADED, OMIT CONTACTS IN CIRCUIT CAVITIES
14,16,18,S AND U

4

ALL PARTS ASSEMBLED IN MEXICO MUST BE STAMPED "ASSY IN MEXICO"
THE WORD "MEXICO" CAN BE SUBSTITUTED ONLY WHERE PART SIZE
PROHIBTS STAMPING "ASSY IN MEXICO", INK STAMP COLOUR WHITE OR HOT
STAMP (NO WHITE TAPE) 115-9009, APPROX. WHERE SHOWN, SIDE OPTIONAL.

5

MATTE TIN PLATED CONTACT TAILS.

6

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

5	-	43	6.552	6.872	7.307	7.012	.437	7.557	6	8-530655-3
5	-	28	4.212	4.532	4.967	4.672	.370	5.217	6	8-530655-2
5	-	36	5.460	5.780	6.215	5.920	.437	6.465	6	8-530655-0
5	-	30	4.524	4.844	5.279	4.984	.437	5.529		7-530655-9
5	-	22	3.276	3.596	4.031	3.736	.370	4.281		7-530655-6
5	-	18	2.652	2.972	3.407	3.112	.370	3.657		7-530655-5
5	-	15	2.184	2.504	2.939	2.644	.370	3.189		7-530655-4
5	-	12	1.716	2.036	2.471	2.176	.370	2.721		7-530655-3
5	-	10	1.404	1.724	2.159	1.864	.370	2.409		7-530655-2
5	-	6	.780	1.100	1.535	1.240	.370	1.785		7-530655-1
	-	18	2.652	2.972	3.407	3.112	.370	3.657		3-530655-4
	1-530655-3	43	6.552	6.872	7.307	7.012	.437	7.557		3-530655-3
	1-530655-2	28	4.212	4.532	4.967	4.672	.370	5.217		3-530655-2
	1-530655-1	44	6.708	7.028	7.463	7.168	.437	7.713		3-530655-1
	1-530655-0	36	5.460	5.780	6.215	5.920	.437	6.465		3-530655-0
	530655-9	30	4.524	4.844	5.279	4.984	.437	5.529	6	2-530655-9
	530655-8	25	3.744	4.064	4.499	4.204	.370	4.749		2-530655-8
	530655-7	24	3.588	3.908	4.343	4.048		4.593		2-530655-7
	530655-6	22	3.276	3.596	4.031	3.736		4.281		2-530655-6
	530655-5	18	2.652	2.972	3.407	3.112		3.657		2-530655-5
	530655-4	15	2.184	2.504	2.939	2.644		3.189		2-530655-4
	530655-3	12	1.716	2.036	2.471	2.176		2.721		2-530655-3
	530655-2	10	1.404	1.724	2.159	1.864		2.409		2-530655-2
	530655-1	6	.780	1.100	1.535	1.240		1.785		2-530655-1
1	PART NO	NO.OF. POSITION	A	B	C	D	W	F	2	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
SEE CALL-OUT

TOLERANCES, UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

FINISH
SEE CALL-OUT

DWN - 19MAR75
CHK - 20MAR75
APVD - 20MAR75

PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

CUSTOMER DRAWING

19MAR75
20MAR75
20MAR75

NAME
HOUSING ASSY, LOW PROFILE,
EDGE CONNECTOR, FLOW SOLDER,
FOR .052 DIA. HOLE .156X.200 CTRS.

SIZE A2
CAGE CODE 00779
DRAWING NO C-530655

RESTRICTED TO -
SCALE 1:1
SHEET 2 OF 2
REV M4

TE Connectivity

TE Connectivity

1471-9 (3/11)