



1		2		3		4	
COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY
△	1 DIS-C-000664	THEK		07.09.06	△		
△					△		
△					△		



- NOTE.1 APPLICABLE CRIMP CONTACT:
RP13A-SC-222(CL113-0151-0)
THIS CONTACT IS FOR
APPLICABLE CABLE AWG#24 TO 28 OR EQUIVALENT.
- 2 APPLICABLE CRIMP CONTACT EXTRACTION TOOL:
RP13A-SC-TP(CL150-0022-8)
- 3 THIS PRODUCT IS DELIVERED DISASSEMBLED.



4	BRASS				
3	POLYCARBONATE	(BLACK) UL94V-0	7	FLEXIBLE POLYVINYL CHLORIDE	(BLACK)
2	POLYCARBONATE	(BLACK) UL94V-0	6	BRASS	(BLACK) CHROMATE TREATMENT (TRIVALENT CHROMIUM) JIS B 1111 M2×0.4×4
1	POLYCARBONATE	(BLACK) UL94V-0	5	STEEL	NICKEL PLATING
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
CODE NO. (OLD) CL			DRAWN M. Ishihara	DESIGNED E. Yumino	CHECKED H. Zemba
			05.09.30	05.09.30	05.09.30
			APPROVED M. Sato		
			05.09.30		
DRAWING NO. EDC4-023504-71			PART NO. RP13A-12PK-15SC(71)		
SCALE 2 : 1			CODE NO. CL113-0219-2-71		
UNITS mm					
HRS					
HIROSE ELECTRIC CO., LTD.					