



LOC	DIST	P	F	REVISIONS		DATE	APPD
				ZONE	LTR		
G	86				U	REV PER 0G3A-0561-01	JR/MS



- 1 CIRCULAR MIL AREA RANGE: 375-450 MCM
- 2 TIN PL 0.00381 [.000150] MIN THK PER ASTM B-545
- 3 NO SIGHT HOLE



DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.51 [.020] 3 PLC DEC ± - ANGLES ± - MATERIAL ANNEALED COPPER ASTM B-75 FINISH △2		DR 02/28/90 DK SCHRUM	AMP AMP INCORPORATED Harrisburg, Pa. 17105	
		CHK 23JAN95 MS FEHER		
		APPD 23JAN95 WJ VOCKROTH	NAME TERMINAL, AMPPOWER™ WIRE SIZE: 400 MCM	
		APPD 23JAN95 TL SHUTTER		
		PRODUCT SPEC 108-30200		
		APPLICATION SPEC -	SIZE C	CAGE CODE 00779
		WEIGHT .308 LB	SCALE 2:1	DRAWING NO 326807
				SHEET 1 OF 1