






- 1 WIRE INSULATION: .470/.425 DIA
- 2 THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.
- 3 BODY: MATERIAL - COPPER ASTM B187 ANNEALED
FINISH - TIN PL PER ASTM B-545 .000150 MIN THK
- 4 INSERT: MATERIAL - BRASS MIL-C-50
FINISH - NICKEL PL PER QQ-N-290 .000300 AVG THK
- 5 FUNNEL: MATERIAL - BRASS MIL-C-50
FINISH - NICKEL PL PER QQ-N-290 .000300 AVG THK

696632-1
PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
INCHES	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± .005
	4 PLC ± -
	ANGLES ± 1°

MATERIAL	FINISH
3 4 5	3 4 5

DWN	02SEP03		TE Connectivity	
CHK	02SEP03			
APVD	02SEP03			
PRODUCT SPEC				
APPLICATION SPEC				
WEIGHT		-		
CUSTOMER DRAWING				

NAME	SEALED COPALUM, RING TONGUE WIRE SIZE : 1/0 AL - 2 CU		
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C=696632	-
SCALE		SHEET	REV
1:1		1 of 1	B