




NOTES:

1. SUPPLIED ON TAPE AND REEL ONLY.

TAPE AND REEL SPECIFICATIONS:

2. TAPE:

MAT'L - ALL CONDUCTIVE POLYSTYRENE CARRIER

ANSI/EIA-481 STANDARD

.630 [16.0] WIDE; .157 [4.0] PITCH

3. REEL:

7.0 [180.00] DIA. 500 PIECES OF

P/N 6100 PER REEL

KEYSTONE ELECTRONICS CORP.

www.keyelco.com • NEW HYDE PARK, NY 11040 • Tel (516) 328-7500

PART NAME

PARALLEL FITTING PIN ON TAPE AND REEL

MATERIAL

AS NOTED

FINISH

AS NOTED

DRN BY

NT

DATE

3.04.19

APP'D

LN

SCALE

X

TOLERANCES

INCH

[MM]

DECIMAL

± .005 [± 0.13]

ANGULAR

± 1°

UNLESS OTHERWISE SPECIFIED

CODE

C






DWG NO.

6100TR


DATE

DESCRIPTION

REV.



ACTUAL SIZE



NOTE:

1. CURRENT RATING: 10A
2. CONTACT RESISTANCE: 20m Ω OR LESS
3. OPERATING TEMPERATURE: -40° TO +125°C

KEYSTONE ELECTRONICS CORP.

www.keyelco.com • NEW HYDE PARK, NY 11040 • Tel (516) 328-7500

PART NAME

PARALLEL FITTING SM PIN

MATERIAL

.016 [0.40] TH'K PHOSPHOR BRONZE

FINISH

GOLD PLATE

DRN BY

NT

DATE

3.04.19

APP'D

RH

SCALE

5X

TOLERANCES

INCH

[MM]

DECIMAL

$\pm .005$ [± 0.13]

ANGULAR

$\pm 1^\circ$

UNLESS OTHERWISE SPECIFIED

CODE

C

DWG NO.

6100

DATE

DESCRIPTION

REV.