


REV.	DATE	DESCRIPTION
NC	01/29/00	INITIAL RELEASE



DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY		
1 BODY	BRASS	GOLD	DRAWN	G.R.S.	01/29/00
2 INSULATOR	TEFLON	NATURAL	CHECKED		
3 CONTACT PIN	BRASS	GOLD	ISSUED		
4 RETAINER RING	BER. COPPER	GOLD	TITLE SMA PLUG TO REVERSE POLARIZED SMA JACK ADAPTOR		
5 GASKET	SILICONE	RED			
6					
7			UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4		
8			DO NOT SCALE DRAWING		
 Connector Corporation SMA PLUG TO REVERSE POLARIZED SMA JACK ADAPTOR					
SIZE			FSCM NO.	DWG. NO.	REV.
A			99001	132171RP.DWG	NC
SCALE			NA	PART NO.	
				132171RP	
				SHEET	
				1	OF 1