







SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
FH2.54-06-01PWS	2*1	0.00	2.54
FH2.54-06-02PWS	2*2	2.54	5.08
FH2.54-06-03PWS	2*3	5.08	7.62
FH2.54-06-04PWS	2*4	7.62	10.16
FH2.54-06-05PWS	2*5	10.16	12.70
FH2.54-06-06PWS	2*6	12.70	15.24
FH2.54-06-07PWS	2*7	15.24	17.78
FH2.54-06-08PWS	2*8	17.78	20.32
FH2.54-06-09PWS	2*9	20.32	22.86
.....			
FH2.54-06-40PWS	2*40	(PIN-1)X2.54	(PIN)X2.54

PART NUMBER DESCRIPTION:

FH2.54-06-NPWS

(D=单排;S=双排)

(Z=直脚;W=弯脚)

(PIN数量;01.....40PIN)

(排针开关)

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:2.54FH H8.5 2xnPin 90度 Y型 PC3.2 PB12.7 6T
			PAR FH2.54-06-NPWS
DECIMALS:	ANGLES:		DWN
X.±0.30	X°±5'		CHKD
X.X±0.20	X.X°±1'	CUSTOMER COPY	APVD
X.XX±0.10	X.XX°±0.5'		SCALE N:A UNIT:MM
		SIZE:A4	SHEET:1F1 REV:A