





RECOMMENDED P.C.B. LAYOUT



▲ 1R BUTTON BLK  
(A800300)

▲ TL1105SPF160R  
(P010204)



## NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
- ▲ 4. CONTACT/TERMINAL MATERIAL: GOLD
5. RATING: 50mA, @12V DC
6. TRAVEL: 0.25±0.1mm
- ▲ 7. OPERATING FORCE: 160±50gf
8. CONTACT RESISTANCE: 100 milliohms Max.
9. ELECTRICAL LIFE: 100,000 CYCLES MIN.
10. ▲ DENOTES CRITICAL PARAMETER.



TITLE

TL1105SPF160R1RBLK

SCALE

4:1

DATE

6/5/19

DR

AR

DWG

XP0268P

REV

A

THE INFORMATION CONTAINED IN THIS DOCUMENT  
IS PROPRIETARY TO E-SWITCH AND IS  
NOT TO BE COPIED OR TRANSFERRED

|      |         |                         |        |      |
|------|---------|-------------------------|--------|------|
| A    | 23920   | RELEASED FOR PRODUCTION | 6/5/19 | MW   |
| REV. | ECN No. | DESCRIPTION             | DATE   | CHKD |