

4

3

2

1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
HB	—					APVD
		F		REMOVED THE RIB ON THE BASE TO CASE ECO-15-011310	19Nov2015	YS.H
						CHL






Diagram dimension	Tolerance
0.99mm max.	±0.1mm
1 - 2.99mm	±0.2mm
3mm min.	±0.3mm



CONNECTION FIGURE




FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING
(BOTTOM VIEW)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	H.Sasaki	TE Connectivity			
		CHK	Y.Oikawa				
		APVD	A.Nagai	NAME OJ-SS-LM SPEC,000 CUSTOMER DRAWING			
		PRODUCT SPEC 製品規格					
		APPLICATION SPEC 取付適用規格					
		WEIGHT		SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
				A3	00779	1461117	
MATERIAL 材料		FINISH 仕上		CUSTOMER DRAWING			
				SCALE 尺度	5:1	SHEET 1 OF 2	REV F

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .

© COPYRIGHT - By - TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

変更

DESCRIPTION

DATE

DWN

APVD

HB

-

P

LTR

SEE SHEET 1

-

-

-

B

3-1419129-1	OJ-SS-124LM, 000	107-79010	24V	OJ-SS-124LM	f
4-1419144-2	OJ-SS-118LM, 000	107-79010	18V	OJ-SS-118LM	e
2-1419129-1	OJ-SS-112LM, 000	107-79010	12V	OJ-SS-112LM	d
1461117-3	OJ-SS-109LM, 000	107-79010	9V	OJ-SS-109LM	c
1440007-1	OJ-SS-106LM, 000	107-79010	6V	OJ-SS-106LM	b
1440007	OJ-SS-105LM, 000	107-79010	5V	OJ-SS-105LM	a
PART NO	DESCRIPTION	PACKAGE SPEC.	PART B	PART A	TYPE

RELAY TYPE

D B NOTE:

1.LOT NO SYSTEM AS FOLLOWING:

WEEK
YEAR

2.TERMINAL DIMENSION IS BEFORE SOLDER DIP;

3.FOR THE TIN-PLATING OF THE PINS:

+0.1mm FOR WIDTH, THICKNESS AND DIAMETER.

+0.5mm FOR LENGTH.

4.USED WELDED CONTACT&LASER MARKING.

5.ADD LOT NO. SYSTEM AS FOLLOWING;

I, DIGITS FOR DAY OF THE WEEK
I II III

1...MONDAY IN THIS WEEK;

2...TUESDAY IN THIS WEEK;

.....

7...SUNDAY IN THIS WEEK

II, DIGITS FOR SHIFT OF THE DAY

1...DAY SHIFT IN THIS DAY;

2...NIGHT SHIFT IN THIS DAY;

III, ONE CHARACTER DISTINGUISH THE
LINE IDENTITY, SUCH AS: A,B.....Z

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

H.Sasaki

CHK

Y.Oikawa

APVD

A.Nagai

PRODUCT SPEC

製品規格

APPLICATION SPEC

取付適用規格

WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

単位: 耗

mm

TOLERANCES UNLESS

OTHERWISE SPECIFIED:

一般公差

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -


ANGLES ± -

FINISH

仕上

MATERIAL

材料



		EPOXY RESIN	SEAL (BASE & BOBBIN)	15
		3UEW	MAGNETIC WIRE	14
94V-0		P.B.T	CASE	13
94V-0		P.B.T	BASE	12
94V-0		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
94V-0		P.P.S	CARD	9
		Ag	MOVABLE CONTACT	8
		Ag	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	Cu ALLOY	NO.TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM



TE Connectivity

NAME

名称

OJ-SS-LM SPEC,000 CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

番号

RESTRICTED TO

REV

A3

00779

C=

1461117

SCALE

尺度

5:1

SHEET

2 of 2

REV

F