

● SHORT CIRCUIT U LINKS

The short circuit U link is a complementary component to the 20-way fixed connector and can be used to make shunts. It is fitted with a rear-mounted 2 mm dia. socket.

CHARACTERISTICS

- Current rating max : 7 A (at 20°C)
- Dielectric withstanding voltage : 2 000 V rms 50 Hz
- Operating voltage : 500 V rms 50 Hz
- Insulation resistance : $\geq 5\,000\text{ M}\Omega$
- Mechanical endurance : > 10 000 matings
- Operating temperature : $-40^{\circ}\text{C} + 70^{\circ}\text{C}$

► Packaging : 100 pieces of the same part number.

Part number	Dimensions (12 mm between axes)
R 644 543 000 / Blue R 644 543 001 / Red R 644 543 002 / Green R 644 543 003 / Black R 644 543 004 / Yellow	

Part number	Dimensions (6 mm between axes)
R 644 543 020* / Blue R 644 543 021* / Red R 644 543 022* / Green R 644 543 023* / Black R 644 543 024* / Yellow	

* Made to order product, please consult Radiall for price and delivery