

M12-P-ACC-HOUSING F REAR MOUNTING



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 302 2000 407
Specification	M12-P-ACC-HOUSING F REAR MOUNTING
HARTING eCatalogue	https://b2b.harting.com/21033022000407

Identification

Category	Accessories
Series	Circular connectors M12
Type of accessory	Housing
Description of the accessory	for rear mounting

Version

Gender	Female
Locking type	Screw locking

Technical characteristics

Tightening torque	2 Nm Lock nut
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition

Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

Commercial data

Packaging size	30
Net weight	16 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140236455
ETIM	EC002943
eCl@ss	27440292 Connector component (accessories)