




- | | |
|---|---|
| 1 | STAMP AMP 4/OW* APPROX AS SHOWN |
| 2 | STAMP AMP 200 APPROX AS SHOWN |
| 3 | MATERIAL THK: $2.59^{+0.08}$ [$.102^{+.003}$] |

321879

PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

170° C MAX

NOT APPLICABLE


WIRE CROSS SECTIONAL AREA RANGE:
96.3-117.0mm²[190,000-231,100] CIR MILS
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

TOLERANCES UNLESS
OTHERWISE SPECIFIED:



0 PLC	$\pm -$
1 PLC	$\pm -$
2 PLC	$\pm 0.20[.008]$
3 PLC	$\pm -$
4 PLC	$\pm -$
ANGLES	$\pm -$

2 TIN PLATE
0.000254[.000100] MIN
THK PER MIL-T-10727

	—
WEIGHT	

CUSTOMER DRAWING



TE Connectivity

NAME	TERMINAL, RING TONGUE, SOLISTRAND TM
------	--

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

A300779C-321879

SCALE	2:1	SHEET	1 OF 1	REV	F1
-------	-----	-------	--------	-----	----