




NOTES:			
1. ALL DIMENSION IN MM [INCH]			
2. GENERAL TOLERANCE: X.X=±0.4			
X.XX=±0.25			
3. TERM. NOS. FOR REF. ONLY			
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC			
350mA, 110V AC/DC			
5. CONTACT RATING (NON-SWITCHING) 5A			
6. CONTACT MATERIAL: SILVER over COPPER ALLOY.			
7. OPERATING FORCE: 425±100 CM/STANDARD			
8. OPERATING TEMP: -30° to 85°C			
9. CIRCUIT SP: 8 POSITIONS, 30° INDEX.			
10. DIELECTRIC STRENGTH 1000V RMS min. @ SEA LEVEL			
11. ▲ DENOTES CRITICAL PARAMETER.			
12. HARDWARE SUPPLIED ON SWITCH— SEE BELOW			
STOPRING, LOCKWASHER & HEX NUT			
CONTACT CONFIGURATION			
Timing: Non-Shorting (BBM)			
TERMINATION DETAIL			
SCALE 2X			
TITLE			
KC18B7.002NLS			
E-SWITCH®			
SCALE			
1.5:1			
DATE			
7/18/03			
DR			
AR			
DWG			
G530171			
REV			
B			
THE INFORMATION CONTAINED IN THIS DOCUMENT			
IS PROPRIETARY TO E-SWITCH AND IS			
NOT TO BE COPIED OR TRANSFERRED			