

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5046930404](#)
Status: **Active**
Overview: [CP Wire-to-Board and Wire-to-Wire Connector Systems](#)
Description: CP-3.3 Receptacle Housing, 3.30mm Pitch, Single Row, Polarized, Positive Inertia Lock, 4 Circuits, Blue

Documents:

3D Model (PDF)	Application Specification AS-504693-002-001 (PDF)
Drawing (PDF)	Packaging Specification SPK-504693-001-001 (PDF)
3D Model	RoHS Certificate of Compliance (PDF)
Product Specification PS-504693-001-001 (PDF)	Product Literature (PDF)
Application Specification AS-504693-001-001 (PDF)	

Agency Certification

UL E29179

General

Product Family	Crimp Housings
Series	504693
Application	Signal, Wire-to-Wire
Overview	CP Wire-to-Board and Wire-to-Wire Connector Systems
Product Name	CP-3.3
UPC	889056226127

Physical

Circuits (maximum)	4
Color - Resin	Blue
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	1314.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.30mm
Pitch - Termination Interface	3.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	AS-504693-001-001, AS-504693-002-001
Packaging Specification	SPK-504693-001-001
Product Specification	PS-504693-001-001
Sales Drawing	5046930000-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[504693](#) Series

Mates With

Plug Housing [5046940404](#)

Use With

Terminal Retainer [504695](#) . Receptacle
Crimp Terminal [50397](#) , [505607](#)