




D



C










B



A

				COLOR	MATERIAL	DESCRIPTION	ITEM NO
		1	1	GREY	PA66-GF15	STD CAP	4
1	1			BLACK	PA66-GF15	STD CAP	
1			1	BURNT RED	VMQ	GROMMET,E-SEAL	3
	1	1		ORANGE-RED	VMQ	GROMMET,N-SEAL	
		1	1	GREY	PA66-GF15	HOUSING	2
1	1			BLACK	PA66-GF15	HOUSING	
1	1	1	/	ORANGE	VMQ	FRONT SEAL	1
				COLOR	MATERIAL	DESCRIPTION	ITEM NO
7.50	7.48	7.48	7.51	WEIGHT OF EACH ASSY NO. (g)			
B	A	A	B	REVISION OF EACH ASSY NO.			
DT06-3S-TE32	DT06-3S-TN32	DT06-3S-TN31	DT06-3S-TE31	DEUTSCH			
1--4	1--3	1--2	1--1	TE PN			
DT06-3S-CE05	DT06-3S-E005-EP06	DT06-3S-E003-EP04	DT06-3S-CE01	COMPARABLE PART			



1	1	1	1	GREY	PA66-GF15	LONG CAP	4
				BLACK	PA66-GF15	LONG CAP	
1			1	BURNT RED	VMQ	GROMMET,E-SEAL	3
	1	1		ORANGE-RED	VMQ	GROMMET,N-SEAL	
		1	1	GREY	PA66-GF15	HOUSING	2
1	1			BLACK	PA66-GF15	HOUSING	
1	1	1	1	ORANGE	VMQ	FRONT SEAL	1
QTY. REQUEST PER ASSY				COLOR	MATERIAL	DESCRIPTION	ITEM NO
8.96	8.94	8.94	8.96	WEIGHT OF EACH ASSY NO. (g)			
B	A	A	B	REVISION OF EACH ASSY NO.			
DT06-3S-TE82	DT06-3S-TN82	DT06-3S-TN81	DT06-3S-TE81	DEUTSCH			
2--4	2--3	2--2	2--1	TE PN			
DT06-3S-CE13	DT06-3S-EP11	DT06-3S-E008	DT06-3S-CE04	COMPARABLE PART			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.64
2 PLC ±0.64
3 PLC ±
4 PLC ANGLES ±
FINISH

DWN C.WAN 15OCT2017
CHK E.JIANG 15OCT2017
APVD I.YIN 15OCT2017

PRODUCT SPEC
108-151009
APPLICATION SPEC
114-151009
WEIGHT SEE TABLES
CUSTOMER DRAWING

SIZE A2
CAGE CODE -
DRAWING NO C-2303816
RESTRICTED TO

SCALE 3:1
SHEET 2 OF 2
REV B

TE Connectivity

DT SERIES, SNAP CAPS
3 WAY PLUG,DT06-3S-TXXX

D

C

B

A