




NOTES: UNLESS OTHERWISE SPECIFIED

1. FOR USE WITH RG-316 OR EQUIVALENT CABLE.
2. MATERIAL SPECIFICATIONS:
INSULATORS: PTFE
SPACER: DELRIN
OUTER CONTACT: BERYLLIUM COPPER
ALL OTHER METAL PARTS: BRASS
3. FINISH SPECIFICATIONS:
CONTACT: .000003 MIN THICK GOLD OVER .000050 MIN THICK NICKEL
ALL OTHER METAL: THIN GOLD OVER .000050 MIN THICK COPPER
4. ELECTRICAL SPECIFICATIONS:
IMPEDANCE: 50 OHMS
FREQUENCY RANGE: DC TO 6 GHz
VSWR: 1.5 MAX
5. CAP, SPACER AND FERRULE SHIPPED LOOSE
6. CRIMP FERRULE (.128 HEX) AND SOLDER TO CONTACT PIN.



CATALOG P/N: 1213A204M

PER ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM) TOLERANCES: DECIMAL: .XX [XX] ± .01 [0.3] XXX [XXX] ± .005 [0.13] XXXX [XXXX] ± .000X ANGLES: ± 2° SCALE: 6:1				 by WINCHESTER Winchester Electronics Corporation 199 Park Road Ext Suite 104 Middlebury, Connecticut 06762			
CUSTOMER SALES DRAWING				MCX R/A CRIMP PLUG (FOR RG-174/U, 188A/U, 316/U)			
DRAWN J	DATE 06/24/2015	APPROVED J	DATE 06/29/2015	THIRD ANGLE 			
APPROVED DCAM	DATE 06/29/2015	APPROVED XXX	DATE XX/XX/XX	A			
1213A204M				SHT 1	OF 1	REV A	