

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20



COPYRIGHT 20



BY -

ALL RIGHTS RESERVED.



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	04SEP2006	YH	JK
	B	REVISED<ECR-15-008612>	11,DEC,15	JY	HG

① 1743445-2





SECTION A-A






② 1-1743445-3

Ⓑ



SECTION A-A



NOTE,

1. GENERAL TOLERANCE : ± 0.4 , $\pm 3^\circ$
2. WARPAGE PERMITTED MAX. -7MM
3. MATING CONNR ASSY PART No.: 1743237
4. APPLICATION TEST SPEC:MS210-06-C (EXCEPT 4.4)

Ⓑ

2	GRAY	PA66-GF30	1-1743445-3
1	BLACK	PA66-GF30	1743445-2
NO	COLOR	MATERIAL	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

JY BAE

CHK

KI LIM

APVD

HG CHO

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC $\pm$
1 PLC $\pm$
2 PLC $\pm$
3 PLC $\pm$
4 PLC $\pm$

ANGLES $\pm$
FINISH

MATERIAL
SEE TABLE



TE Connectivity

NAME
LEVER HSG FOR SHIELD 60POS.
(FOR HD,MG,UN)

SIZE

A2

CAGE CODE

00779

DRAWING NO

C-1743445

RESTRICTED TO
HMC/KMC
(KIC)

SCALE

1:1

SHEET

1

OF

1

REV

B