


REVISIONS					
ZONE	LTR	ECN	DESCRIPTION	DATE	APPROVED
	F	23719	REVISED & REDRAWN	6-8-79	LMC
	G	36837	ITEM 5 WAS 003-0064-0000	3-31-97	PS
	H	38846	UPDATE REV. LETTER	4-15-97	PS



Tyco Dwg 3-1532004-9
Micro P/N 032-0077-0001

- NOTES: UNLESS OTHERWISE SPECIFIED,
- THIS CONNECTOR MATES WITH ALL SLIDE-ON SERIES JACKS AND RECEPTACLES AS LISTED IN MALCO CATALOG.
 - SILVER PLATE .0002 MIN. PER QQ-S-365, TYPE II, GRADE A.
 - GOLD PLATE PER MIL-G-45204, TYPE II, GRADE C, CLASS I.
 - FOR ASSEMBLY INSTRUCTIONS, SEE RF-ASMB-102
 - INNER CONDUCTOR IS SOLDERED TO PIN CONTACT.
 - CABLE ACCEPTANCE DIM'S
JACKET DIA. .134 MAX
SHIELD DIA. .118 MAX
DIELECTRIC DIA. .100 MAX
INNER COND. DIA. .015 MAX
 - SUBASSEMBLY MATERIAL SPEC: FERRULE, BRASS PER QQ-B-626; SPRING FINGER, BERYLLIUM COPPER PER QQ-C-533.
 - MALCO ASSEMBLY TOOL # 010-1008-0000 REQUIRED.

	1		003-0272-0000	B. R. CAP	SILICONE RUBBER, ZZ-R-765	5
3	1		003-0360-0002	CONTACT, PIN	BRASS, QQ-B-626	4
	1		000-0301-0125	INSULATOR	TEFLON PER L-P-403	3
2	1		000-5301-0007	JERK RING	BRASS, QQ-B-626	2
7	1		003-1517-0001	SUBASSEMBLY		1
	QTY REQD	CODE IDENT	PART OR IDENTIFYING NO.	DESCRIPTION	MATERIAL & SPEC.	ITEM NO.

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
FRACTIONS DECIMALS ANGLES
± .XX ± .010 ±

MATERIAL
NOTED
FINISH
NOTED
DO NOT SCALE DRAWING

CONTRACT NO.
APPROVALS
DRAWN *Ingutierrez* 10-6-78
CHECKED *LMC* 11/2/78
PR. ENG. *MM* 5-30-77
APPD.



MALCO
A MICRODOT COMPANY, INC.
220 PASADENA AVE., SO. PASADENA, CALIF. 91030

STRAIGHT PLUG, 93 OHM

SIZE C CODE IDENT NO. 98278 DRAWING NO. 032-0077-0001

SCALE 10X

SHEET 1 OF 1