


LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			U1	REVISED PER ECO-11-004917	11MAR11	RK HMR

AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED



- 1 STAMP AMP 22-16* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC MIL-T-7928
COMMERCIAL WIRE RANGE IS 22-16
- 2 WIRE INSULATION DIA: 2.67-3.56 [.105-.140]
- 3 TONGUE MATERIAL THK: 0.79^{±0.05} [.031^{±.002}]
- 4 MATERIAL: BODY - CU PER ASTM B152
SLEEVE - PVC, COLOR - RED
- 5 MATERIAL: BODY - CU PER ASTM B152
SLEEVE - PVC, COLOR - BLACK
- 6 REPLACED BY 8-34146-1

OBSOLETE	100	LOOSE PC,BOX SPL		8-34146-6	
	50	LOOSE PC,BAG		8-34146-5	
	5	LOOSE PC,BLS		8-34146-4	
	100	LOOSE PC,BOX		8-34146-1	
	5000	ON TAPE, REEL		2-34146-5	
	1000	LOOSE PIECE		2-34146-4	
	5000	ON TAPE, REEL		2-34146-1	
	1000	LOOSE PIECE		34146	
	QTY	PACKAGE TYPE		PART NO.	

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 08/06/92 DK SCHRUM		 TE Connectivity										
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600V MAX (1000V FIXTURE OR SIGN)		DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK 11/10/92 RE HERSEY		NAME							
FOR APPLICATION		TOOLING ASSISTANCE CENTER		CIRCULAR MIL AREA:				0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD 11/10/92 M BARNABA		TERMINAL, RING TONGUE, PLASTI-GRIP, WIRE SIZE, 22-16 AWG							
TOOLING INFORMATION		1-800-722-1111		0.26-1.65mm² [509-3260] SOLID OR STRANDED						PRODUCT SPEC UL 486A									
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL SEE NOTES		FINISH TIN PER ASTM B545		APPLICATION SPEC —		SIZE A3		CAGE CODE 000779		DRAWING NO C-34146		RESTRICTED TO —	
										WEIGHT —									
										CUSTOMER DRAWING				SCALE 4:1		SHEET 1 of 1		REV U1	