




1. CONNECTOR ACCEPTS SIZE 20 DF PIN CONTACTS, RETENTION TINES ARE AN INTEGRAL PART OF INSERT.
2. CONNECTOR COMPLIES WITH 108-40005 WHERE APPLICABLE.
- ③ MOLDED PARTS: GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL94V-0 RATED. COLOR: BLACK
- ④ SHELLS: STEEL PER ASTM A109.
- ⑤ TIN OR TIN-LEAD PLATED OVER COPPER UNDERPLATE.
- ⑥ TIN PLATED OVER COPPER UNDERPLATE.

		STANDARD		NO	.120	207464-7
	OBSOLETE	SMALL PACK		YES	.120	207464-6
SUPERSEDED BY 207464-2		STANDARD		YES	.154	207464-4
SUPERSEDED BY 207464-2		STANDARD		NO	.154	207464-3
		STANDARD		YES	.120	207464-2
SUPERSEDED BY 207464-7		STANDARD		NO	.120	207464-1
		PACKAGING TYPE	SHELL FINISH	GROUNDING INDENTS	A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.WELDON 7-19-85 CHK J.GERACE 7-29-85		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		NAME PLUG CONNECTOR, SIZE 3, 25 POSITION, AMPLIMITE™ HDP —	
MATERIAL		FINISH		SIZE	RESTRICTED TO
SEE NOTES		SHELLS: SEE TABLE		CAGE CODE A2 00779	DRAWING NO C-207464
		WEIGHT —		SCALE 4:1 SHEET 1 of 1 REV J	
CUSTOMER DRAWING					