







PCB.WELDING DRAWING (TOLERANCE:±0.05)

型号	塑体颜色	Main technical performance	
PJ-3170-5PB	黑色	Rated electrical load	DC 30V 0.5A
PJ-3170-5PG	绿色	Contact resistance	≤0.03Ω
PJ-3170-5PL	粉色	Insulation resistance	≥100MΩ DC250V
PJ-3170-5PD	蓝色	Pressure resistance	AC 500V 1min
		Insertion force	3-20N
		Operating temperature range	-20℃~+70℃
		service life	5000h

7	后盖	1	PBT	配色
6	基座	1	PBT	配色
5	5#接脚	1	QSn6.5-0.1锡青铜带 0.30mm	铜锡
4	4#接脚	1	H62(Y) 黄铜带 0.40mm	铜锡
3	3#接脚	1	H62(Y) 黄铜带 0.40mm	铜锡
2	2#接脚	1	QSn6.5-0.1锡青铜带 0.30mm	铜锡
1	1#接脚	1	H62(Y) 黄铜带 0.40mm	铜锡
LTR	PART NAME	QTY	MATERIAL	REMARK

MANUFACTURE DWG



东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,Ltd



TITLE:

Ø3.5系列耳机插座

PAR

DWN

CHKD

SCALE N:A

UNIT:M

SHEET:

REV:A