









PANEL MOUNTING

| SWITCH FUNCTION |        |
|-----------------|--------|
| POS. 1          | POS. 2 |
|                 |        |
| OFF             | ON     |
| OPEN            | 1-2    |



## NOTE:

1. DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
- ▲ 5. CONTACT RATING: 16A @ 125VAC [UR, cUR]  
10A @ 250VAC [UR, cUR]  
1/3HP 125/250VAC [UR, cUR]  
6(2)A 250V~ 1E4 T125/55 [ENEC14]
6. CONTACT RESISTANCE: 35mΩ MAX. @ 50VAC
7. INSULATION RESISTANCE: 1000MΩ MIN. @ 500VAC
8. DIELECTRIC STRENGTH: 1,500VAC FOR 1 MINUTE
9. ELECTRICAL LIFE: 6,000 CYCLES [UR, cUR, NOM]  
10,000 CYCLES [ENEC14]
10. OPERATING TEMPERATURE: -20°C TO 105°C [UR, cUR, NOM]  
-20°C TO 125°C [ENEC14]
11. ▲ DENOTES CRITICAL PARAMETER
12. 2011/65/EU (ROHS) COMPLIANT

▲ MARKING COLOR:  
BLACK▲ HOUSING COLOR:  
WHITE▲ ACTUATOR COLOR:  
WHITE

E-SWITCH®

|     |        |                      |         |     |
|-----|--------|----------------------|---------|-----|
| B   | 23472  | REMOVED SEMKO RATING | 7/24/18 | MJR |
| A   | 22356  | NEW RELEASE          | 6/16/16 | MJR |
| REV | PCR NO | DESCRIPTION          | DATE    | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE RRG311C2211

SCALE  
2:1DATE  
6/16/2016DR  
MJRDWG  
38-RRG311C2211REV  
B