




4

3

2

1

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

MAR , 2006.

© COPYRIGHT 2009 By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

IR

-

-

SEE SHEET 1

-

-

-

CONNECTOR

BOX

314mm(L)*128mm(W)*11mm(H)

OUTER CARTON

340mm(L)*295mm(W)*320mm(H)

CORRUGATE PAPER

INNER CARTON

320mm(L)*138mm(W)*144mm(H)

OBSOLETE		5040	1260	105	40	9	-	-	9
OBSOLETE		4320	1080	90	50	9	-	-	8
OBSOLETE		4320	1080	90	48	9	-	-	7
OBSOLETE		4320	1080	90	46	9	-	-	6
OBSOLETE		4320	1080	90	44	9	-	-	5
OBSOLETE		5040	1260	105	42	9	-	-	4
OBSOLETE		5040	1260	105	40	9	-	-	3
OBSOLETE		5040	1260	105	38	9	-	-	2
OBSOLETE		5760	1440	120	36	9	-	-	1
OBSOLETE		5760	1440	120	34	9	-	-	0
OBSOLETE		6480	1620	135	32	8	-	-	9
OBSOLETE		7200	1800	150	30	8	-	-	8
OBSOLETE		7200	1800	150	28	8	-	-	7
OBSOLETE		7920	1980	165	26	8	-	-	6
OBSOLETE		8640	2160	180	24	8	-	-	5
OBSOLETE		9360	2340	195	22	8	-	-	4
OBSOLETE		10080	2520	210	20	8	-	-	3
OBSOLETE		11520	2880	240	18	8	-	-	2
OBSOLETE		12960	3240	270	16	8	-	-	1
OBSOLETE		15120	3780	315	14	8	-	-	0
OBSOLETE		17280	4320	360	12	7	-	-	9
OBSOLETE		20880	5220	435	10	7	-	-	8
OBSOLETE		26640	6660	555	8	7	-	-	7
OBSOLETE		35280	8820	735	6	7	-	-	6
OBSOLETE		51840	12960	1080	4	7	-	-	5
OBSOLETE		4320	1080	90	50	7	-	-	4
OBSOLETE		4320	1080	90	48	7	-	-	3
OBSOLETE		4320	1080	90	46	7	-	-	2
OBSOLETE		4320	1080	90	44	7	-	-	1
OBSOLETE		5040	1260	105	42	7	-	-	0
OBSOLETE		5040	1260	105	40	6	-	-	9
OBSOLETE		5040	1260	105	38	6	-	-	8
OBSOLETE		5760	1440	120	36	6	-	-	7
OBSOLETE		5760	1440	120	34	6	-	-	6
OBSOLETE		6480	1620	135	32	6	-	-	5
OBSOLETE		7200	1800	150	30	6	-	-	4
OBSOLETE		7200	1800	150	28	6	-	-	3
OBSOLETE		7920	1980	165	26	6	-	-	2
OBSOLETE		8640	2160	180	24	6	-	-	1
OBSOLETE		9360	2340	195	22	6	-	-	0
OBSOLETE		10080	2520	210	20	5	-	-	9
OBSOLETE		11520	2880	240	18	5	-	-	8
OBSOLETE		12960	3240	270	16	5	-	-	7
OBSOLETE		15120	3780	315	14	5	-	-	6
OBSOLETE		17280	4320	360	12	5	-	-	5
OBSOLETE		20880	5220	435	10	5	-	-	4
OBSOLETE		26640	6660	555	8	5	-	-	3
OBSOLETE		35280	8820	735	6	5	-	-	2
OBSOLETE		51840	12960	1080	4	5	-	-	1

OBSOLETE		5040	1260	105	40	4	-	-	9
OBSOLETE		4320	1080	90	50	4	-	-	8
OBSOLETE		4320	1080	90	48	4	-	-	7
OBSOLETE		4320	1080	90	46	4	-	-	6
OBSOLETE		4320	1080	90	44	4	-	-	5
OBSOLETE		5040	1260	105	42	4	-	-	4
OBSOLETE		5040	1260	105	40	4	-	-	3
OBSOLETE		5040	1260	105	38	4	-	-	2
OBSOLETE		5760	1440	120	36	4	-	-	1
OBSOLETE		5760	1440	120	34	4	-	-	0
OBSOLETE		6480	1620	135	32	3	-	-	9
OBSOLETE		7200	1800	150	30	3	-	-	8
OBSOLETE		7200	1800	150	28	3	-	-	7
OBSOLETE		7920	1980	165	26	3	-	-	6
OBSOLETE		8640	2160	180	24	3	-	-	5
OBSOLETE		9360	2340	195	22	3	-	-	4
OBSOLETE		10080	2520	210	20	3	-	-	3
OBSOLETE		11520	2880	240	18	3	-	-	2
OBSOLETE		12960	3240	270	16	3	-	-	1
OBSOLETE		15120	3780	315	14	3	-	-	0
OBSOLETE		17280	4320	360	12	2	-	-	9
OBSOLETE		20880	5220	435	10	2	-	-	8
OBSOLETE		26640	6660	555	8	2	-	-	7
OBSOLETE		35280	8820	735	6	2	-	-	6
OBSOLETE		51840	12960	1080	4	2	-	-	5

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

O.HU

23-MAR-2006

CHK

S.HDU

23-MAR-2006

APVD

W.J.KE

23-MAR-2006

PRODUCT SPEC

108-57197

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

SCALE

1:1

SHEET

2 OF 2

REV

B1

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

± -

1 PLC

± 0.15

2 PLC

± 0.10

3 PLC

± 0.05

4 PLC

± -

ANGLES

± 3°

MATERIAL

SEE SHEET 1

FINISH

SEE SHEET 1

STE

TE Connectivity

AMPMODU 2.0mm PITCH,REC

CONN,VERTICAL,MOUNT TYPE

SIZE

A3

CAGE CODE

—

DRAWING NO

C-1734506

RESTRICTED TO

—