





WIRING FACE



MATING FACE



ECHELLE 3/1



ECHELLE 2/1

NOTES

MATERIALS

SHELL
COUPLING LATCH
O'RING

SEE TABLE
STAINLESS STEEL
LUBRICATED RED SILICON

PERFORMANCES CHARACTERISTICS

MECHANICAL

TEMPERATURE CLASS
DURABILITY
SEALING IN MATED CONDITIONS

SEALING IN UNMATED CONDITIONS
OPEN FACE SEALING
POLLUTION DEGREE
CORROSION SALT SPRAY
FLAMMABILITY
OUTDOOR SUITABILITY (UV RESIST)
SCOOP PROOF

IEC61984/UL1977
IEC61984
IEC60529
DIN40050

IEC60529
IEC60529
IEC61984

UL94
UL746C

-40°C TO 105°C
500 MATE / UNMATE CYCLES
IP68 1BAR DURING 1WEEK
IP69K
IP67 WITH CAPS
IP67 WITH R*M25* CONTACTS
4
MIN 1000H
MATERIAL RATING: 5VA
MATERIAL RATING: (f1)

ELECTRICAL

TOUCH PROOF
NOMINAL CURRENT

NOMINAL CURRENT

IEC60529
UL1977

IEC61984

IP2X
16A WITH AWG14 WIRE / 13A
WITH AWG16 WIRE
16A WITH 2.5MM² WIRE / 13A
WITH 1.5MM² WIRE AT 60°C

NOMINAL VOLTAGE
NOMINAL VOLTAGE

UL1977
IEC61984
IEC61984

600V
250VAC 4KV 4 FOR CLASS II
500VAC 6KV 4 FOR CLASS I

CONNECTOR BREAKING CAPACITY

UL1977
IEC61984

277V 13A WITH AWG14/16 WIRES
250VAC 13A 4KV 4

ROHS COMPLIANT

- COUNTERPART REFERENCE UTL RECEPTACLE
- CONNECTORS ARE DELIVERED AS PRE-ASSEMBLED KIT
- CONNECTOR BLOCKS ACCEPTS TRIM TRIO CONTACTS #16, R*M* OR S*M* TYPES
- CONTACTS TO BE ORDERED SEPARATELY.
- WARNING: PHASE CONTACTS ARE MALE VERSION AND GROUND CONTACT IS FEMALE VERSION
- UNIT IN MM

P/N	SHELL' S MATERIAL
UTL6103G1P	POLYAMID GLASS REINFORCED BLACK COLOR
UTL6103G1P03	POLYAMID GLASS REINFORCED LIGHT GREY COLOR

P/N : SEE TABLE

d	19/11/12	Change part number customer drawing UTS2-0009A-C01 by UTL1-0009A-C01	22725
ISS	DATE	Latest modification - by: RIOUX.B	MOD N°
Designed by:	RAGAINÉ M.	Date: 06/12/11	CUSTOMER DRAWING
TITLE	MALE PLUG LAYOUT 4 CONTACTS UTL CONNECTOR		
Scale 1/1		General linear Tolerances: ± 0,3	NPRDS / PROJECT UTL
	WWW.SOURIAU.COM		This document is the property of SOURIAU It must not be reproduced or communicated without permission
FORMAT A2	SOURIAU DRG N° UTL1-0009A-C01		SHEET 1/1