







SIGN	DATE	DESCRIPTION	APPROVER
△	2010.04.26	The normal grey No. changed from RAL7004/P to RAL7035/D	Jacke
△	2010.04.26	The dimensions is changed from $\phi 1.40$ to $\phi 1.60$	Jacke
△	2010.06.19	The design is changed	Chen Bo
△	2010.09.20	The Material is changed from Brass to Copper	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ③ Male contact pin: Copper Tin plated
- Item ① Terminal(housing): Thermoplastic (UL94V-0)

Electrical:

- Voltage rating: 300V
- Current rating: 20A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to $+115^{\circ}\text{C}$
- Soldering temperature: $250^{\circ}\text{C} \pm 10^{\circ}\text{C}/5 \text{ Sec}$
- Safety Approval: us

EU 04 70 x 0 xxxx G

- COLOR
- 0 Black (RAL9005)
 - 2 Red (RAL3001/D)
 - △ 3 Orange(RAL2011/P)
 - 4 Yellow(RAL1018/A)
 - 5 Green(RAL6018/T)
 - 6 Blue (RAL5015/A)
 - 8 Grey(RAL7035/D)

G: Pb<40,000ppm

0000 Standard @ Logo
000A Standard ANY Logo
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		EU 5.0 SERIES 4P (Right)				
PART NO.	EU0470x0xxxxG			DWG NO.	8EU0003	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		
			Chen Bo 2010.09.20			
					UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30
						X.XX ±0.10
						X° ±1°