

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

(C) COPYRIGHT






ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

| P  | LTR     | DESCRIPTION   | DATE    | DWN | APVD |
|----|---------|---------------|---------|-----|------|
| E4 | REVISED | ECR-21-107353 | 14JUL21 | T.Q | N.S  |




注 記

- 適用電線範囲: AWG #26&#28  
被覆外径:  $\phi 0.8\text{mm} \sim \phi 0.95\text{mm}$
- 材料: ハウジング-ガラス入りナイロン UL94V-0、色: グレー、青  
コンタクト-錫めっき済み、りん青銅
- ハウジング ロック:  
2極は、1箇所 3~20極は、2箇所
- ゲート口は左付きと右付きが存在する。(2極品を除く)

NOTES:

- APPLICABLE WIRE SIZE: AWG #26&#28  
INSULATION DIA RANGE:  $\phi 0.8\text{mm} \sim \phi 0.95\text{mm}$
- MATERIAL:  
HOUSING: NYLON(G.F.) UL94V-0, COLOR: GRAY, BLUE  
CONTACT: PRE-TIN PHOS-BRONZE
- HOUSING LOCK:  
2 POSITION - SINGLE LOCK  
3 TO 20 POSITIONS - DOUBLE LOCK
- CONNECTOR HAVE THE GATE LEFT SIDE AND RIGHT SIDE. (EXCEPT 2Pos.)

|                                                                                       |  |                                                                 |  |                                                                                                       |  |                                                                                 |                    |
|---------------------------------------------------------------------------------------|--|-----------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------|--------------------|
|                                                                                       |  | DWN 12. JUL '96<br>T. FURUYA                                    |  |  TE Connectivity |  |                                                                                 |                    |
|                                                                                       |  | CHK 12. JUL '96<br>J. TANIGAWA                                  |  |                                                                                                       |  |                                                                                 |                    |
| DIMENSIONS:<br>単位: 毫<br>mm                                                            |  | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED                        |  | APVD S. Kurohachi 9/15 99                                                                             |  | NAME<br>名称                                                                      |                    |
|  |  | 一般公差<br>10W ±0.2<br>30W >10 ±0.25<br>100W >30 ±0.3<br>ANGLE ±3° |  | PRODUCT SPEC<br>製品規格<br>108-5525                                                                      |  | AMP Mini Common Terminated (CT) Connector 1.5mm PITCH<br>MT RECEPTACLE ASSEMBLY |                    |
|                                                                                       |  |                                                                 |  | APPLICATION SPEC<br>取付適用規格<br>114-5223                                                                |  |                                                                                 |                    |
| MATERIAL<br>材料<br>SEE NOTE 2<br>注記2参照                                                 |  | FINISH<br>仕上<br>SEE NOTE 2<br>注記2参照                             |  | WEIGHT<br>重量<br>SEE TABLE 表参照                                                                         |  | SIZE<br>A3                                                                      | CAGE CODE<br>00779 |
|                                                                                       |  |                                                                 |  | CUSTOMER DRAWING                                                                                      |  | DRAWING NO<br>番号<br>C-353293                                                    |                    |
|                                                                                       |  |                                                                 |  |                                                                                                       |  | SCALE<br>尺度<br>NON                                                              | SHEET<br>1 OF 2    |
|                                                                                       |  |                                                                 |  |                                                                                                       |  | REV<br>E4                                                                       |                    |

RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT

ALL RIGHTS RESERVED.

| LOC | DIST | REVISIONS   |      |     |      |
|-----|------|-------------|------|-----|------|
| P   | LTR  | DESCRIPTION | DATE | DWN | APVD |
|     |      | SEE SHEET 1 |      |     |      |

|            |                |      |      |      |             |            |            |
|------------|----------------|------|------|------|-------------|------------|------------|
| 0.97       | 31.5           | 30.5 | 28.5 | 20   | 7-353293-0  | 4-353293-0 | 2-353293-0 |
| 0.92       | 30.0           | 29.0 | 27.0 | 19   | 6-353293-9  | 3-353293-9 | 1-353293-9 |
| 0.87       | 28.5           | 27.5 | 25.5 | 18   | 6-353293-8  | 3-353293-8 | 1-353293-8 |
| 0.83       | 27.0           | 26.0 | 24.0 | 17   | 6-353293-7  | 3-353293-7 | 1-353293-7 |
| 0.78       | 25.5           | 24.5 | 22.5 | 16   | 6-353293-6  | 3-353293-6 | 1-353293-6 |
| 0.73       | 24.0           | 23.0 | 21.0 | 15   | 6-353293-5  | 3-353293-5 | 1-353293-5 |
| 0.68       | 22.5           | 21.5 | 19.5 | 14   | 6-353293-4  | 3-353293-4 | 1-353293-4 |
| 0.64       | 21.0           | 20.0 | 18.0 | 13   | 6-353293-3  | 3-353293-3 | 1-353293-3 |
| 0.59       | 19.5           | 18.5 | 16.5 | 12   | 6-353293-2  | 3-353293-2 | 1-353293-2 |
| 0.54       | 18.0           | 17.0 | 15.0 | 11   | 6-353293-1  | 3-353293-1 | 1-353293-1 |
| 0.49       | 16.5           | 15.5 | 13.5 | 10   | 6-353293-0  | 3-353293-0 | 1-353293-0 |
| 0.45       | 15.0           | 14.0 | 12.0 | 9    | 5-353293-9  | 2-353293-9 | 353293-9   |
| 0.40       | 13.5           | 12.5 | 10.5 | 8    | 5-353293-8  | 2-353293-8 | 353293-8   |
| 0.35       | 12.0           | 11.0 | 9.0  | 7    | 5-353293-7  | 2-353293-7 | 353293-7   |
| 0.30       | 10.5           | 9.5  | 7.5  | 6    | 5-353293-6  | 2-353293-6 | 353293-6   |
| 0.26       | 9.0            | 8.0  | 6.0  | 5    | 5-353293-5  | 2-353293-5 | 353293-5   |
| 0.21       | 7.5            | 6.5  | 4.5  | 4    | 5-353293-4  | 2-353293-4 | 353293-4   |
| 0.16       | 6.0            | 5.0  | 3.0  | 3    | 5-353293-3  | 2-353293-3 | 353293-3   |
| 0.11       | 4.5            | 3.5  | 1.5  | 2    | 5-353293-2  | 2-353293-2 | 353293-2   |
| WEIGHT (g) | C              | B    | A    | Pos. | BLUE        | BLACK      | GRAY       |
|            | 寸 法 DIMENSIONS |      |      |      | 製 品 型 番 P/N |            |            |

|                                                                                                                                       |  |                                                                                                                                                                        |  |                                                                                                                                                                                                 |  |                                                                                                                                                                                |  |                                                                  |  |
|---------------------------------------------------------------------------------------------------------------------------------------|--|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|------------------------------------------------------------------|--|
| DIMENSIONS:<br>単位: mm<br>TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>一般公差<br>10 ± : ±0.2<br>30 ± : ±0.25<br>100 ± : ±0.3<br>ANGLE : ±3° |  | DWN T. FURUYA 12. JUL '96<br>CHK J. TANIGAWA 12. JUL '96<br>APVD<br>PRODUCT SPEC<br>製品規格<br>108-5525<br>APPLICATION SPEC<br>取付適用規格<br>114-5223<br>WEIGHT SEE TABLE 表参照 |  | WIRE RANGE<br>絶合電線断面積<br>0.08mm <sup>2</sup> -0.14mm <sup>2</sup><br>INSULATION DIA<br>被覆外径<br>Ø0.8mm-Ø0.95mm<br>MATERIAL SEE SHEET 1 OF 2<br>材料   枚目参照<br>FINISH SEE SHEET 1 OF 2<br>仕上   枚目参照 |  | TE Connectivity<br>NAME<br>AMP Mini Common Terminated (CT) Connector 1.5mm PITCH<br>MT RECEPTACLE ASSEMBLY<br>SIZE<br>A4<br>CAGE CODE<br>00779<br>DRAWING NO<br>番号<br>C=353293 |  | CUSTOMER DRAWING<br>SCALE<br>尺度<br>NON<br>SHEET 2 OF 2<br>REV E4 |  |
|---------------------------------------------------------------------------------------------------------------------------------------|--|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|------------------------------------------------------------------|--|