

\* UNLESS OTHERWISE SPECIFIED TOLERANCES  
ON DECIMAL IS:

SIZE	DIMENSIONS(mm/in)				
	A		B		C
	MM ( $\pm 0.50$ )				
9	MM ( $\pm 0.02$ )				
	INCH ( $\pm 0.02$ )				
15	MM 31.50	MM 24.99	MM 40.50	MM 15.00	
	INCH 1.240	INCH 0.984	INCH 1.594	INCH 0.591	
25	MM 40.00	MM 33.32	MM 40.50	MM 15.00	
	INCH 1.575	INCH 1.312	INCH 1.594	INCH 0.591	
37	MM 54.00	MM 47.04	MM 49.50	MM 15.00	
	INCH 2.126	INCH 1.852	INCH 1.949	INCH 0.591	
	MM 70.50	MM 63.50	MM 54.50	MM 16.00	
	INCH 2.776	INCH 2.500	INCH 2.146	INCH 0.630	

PLASTIC: ABS UL 94-HB RATED  
JACKSCREWS: STEEL-BLACK OXIDE FINISH  
M3 HOODSCREWS: STEEL-BLACK OXIDE FINISH  
COMPRESSION INSERTS: ABS UL 94-HB RATED  
M3 NUTS: STEEL-BLACK OXIDE FINISH  
OPERATING TEMP: -30°C TO +90°C

## BACKSHELL KIT INCLUDES:

(2)BACKSHELL HALVES  
(2)4-40 THUMBSCREWS  
(2)HOUSING SCREWS & (2)NUTS  
(1)SET OF COMPRESSION INSERTS-VARIOUS SIZES  
DIAMETERS:4mm(.157"),5mm(.197"),7mm(.276"),9mm(.351")

NOTE: 37 POSITION HAS (4) HOUSING  
SCREWS & (4)NUTS

\*\*NOTE: 3 in-lbs IS RECOMMEND TORQUE FOR HOUSING SCREWS

970-YYY-010R011  
 SERIES \_\_\_\_\_  
 POSITIONS \_\_\_\_\_  
 009  
 015  
 025  
 037  
 MATERIAL \_\_\_\_\_  
 010 = PLASTIC  
 COLOR \_\_\_\_\_  
 01 = BLACK  
 PUT-UPS \_\_\_\_\_  
 1 = KIT

RoHS COMPLIANT

UNITS = "as specified" DO NOT SCALE FROM DRAWING





THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OR SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
PAM JENKINS  
DATE:  
06/09/2005

NorComp

SCALE: NTS SHEET 1 OF 2 REV 12  
DWG NO. 970-YYY-010R011



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OR SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
PAM JENKINS  
DATE:  
06/09/2005

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	SHEET 2	OF 2	REV 12
DWG NO. 970-YYY-010R011			