



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED PER ECO-14-012833	21AUG2014	NK	DR
	B2	REVISED PER ECO-17-008806	20FEB2018	RS	DR



AMP WIRE RANGE	E13288 Listed
12-10 AWG SOLID OR STRANDED	12-10 AWG STRANDED

LR7189 Certified	MILITARY P/N AND CLASS
12-10 AWG SOLID OR STRANDED	NOT APPLICABLE

- 1 STAMP AMP 12-10* APPROX AS SHOWN.
- 2 NOTE DELETED



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C [338°F] MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
		WIRE CROSS SECTIONAL AREA RANGE: 2.62-6.64mm ² [5,180-13,100] CIR MILS SOLID OR STRANDED
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.
FOR ORDER ENTRY	1-800-526-5142	

500	LOOSE PIECE	31805
QTY	PACKAGE TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-17-93	 TE Connectivity Ltd.						
		CHK DA PATTERSON 3-17-93							
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD DE MILLER 3-17-93	NAME						
	0 PLC ± -	PRODUCT SPEC	TERMINAL, RING TONGUE, SOLISTRAND™ 12-10 AWG						
	1 PLC ± -	UL 486 A-B							
	2 PLC ± -	APPLICATION SPEC							
	3 PLC ± 0.127[.005]	—							
	4 PLC ± -	—							
ANGLES ± -			SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO		
MATERIAL COPPER PER ASTM B-152 ANNEALED	FINISH TIN PLATE 0.00254[.000100] MIN THK PER ASTM B545	WEIGHT	A2	00779	C-31805		—		
CUSTOMER DRAWING			SCALE		1:1	SHEET	1 of 1	REV	B2