





Minimum cable diameter: $\phi F_{max} = 3$
Maximum cable diameter:
- with rubber bushing: $\phi F_{max} = 6,5$
- without rubber bushing: $\phi F_{max} = 8,5$
- without reduction plate: $\phi F_{max} = 12,5$



All Dimensions in mm
Original Size DIN A4



All rights reserved
Department EC PD - FR

HARTING Electronics GmbH
D-32339 Espelkamp

Scale
1:1

Free size tol.

Ref.

Sub.

Created by
DOUGE

Inspected by
BAGDIKIAN

Standardisation
KOHLER

Date
2013-01-29

State
Final Release

Title
D-Sub Hood 25P side entry full metal

Doc-Key / ECM-Nr.
100521735/UGD/001/A
500000056836

Type
TB

Number
09670250334

Rev.
A

Page
1/1

09670250334

4-40UNC

Part number

screw thread