

R 15-EG-13,5-AL



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 000 0121
Specification	R 15-EG-13,5-AL
HARTING eCatalogue	https://b2b.harting.com/09150000121

Identification

Category	Hoods/Housings
Series	R 15
Type of hood/housing	Screw mounted housing
Description of hood/housing	Straight

Version

Locking type	Screw locking
--------------	---------------

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Aluminium
Material (seal)	NBR
RoHS	compliant with exemption
RoHS exemptions	6(b) / 6(b)-II: Lead as an alloying element in aluminium containing up to 0,4 % lead by weight / Lead as an alloying element in aluminium for machining purposes with a lead content up to 0,4 % by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes

Material properties

REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
	Lead
	Naphthalene

Commercial data

Packaging size	10
Net weight	20.2 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440224 Shell for circular connectors