






NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 12VDC, 50mA
- ▲ 5. OPERATING FORCE: 100 ± 50 gf
6. TRAVEL: 0.25 +0.2/-0.1 mm
7. CONTACT RESISTANCE: 50 MILLI OHMS MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE 100,000 CYCLES MIN.
- ▲ 9. CONTACT MATERIAL: SILVER
10. ▲ DENOTES CRITICAL PARAMETER
11. OPERATING TEMP: -40°C TO 85°C



C	24551	REMOVE STEP IN HOUSING, CHANGE TEMP	10/29/20	JM	 E-SWITCH®				
B	18313	LEG TOLERANCE WAS +/- 0.1	11/12/08	BLR					
A	12370	RELEASED FOR PRODUCTION	8/14/02	CJB	TITLE TL1105SF100Q				
REV	PCR NO	DESCRIPTION	DATE	BY	SCALE 4:1 DATE 12/17/1997 DR BLR DWG P020307 REV C				
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED									