

D

C

B



A

D




C

B

A



DETAIL A



DETAIL B

OBSOLETE 5	STANDARD	NO	3.81 [.150] DIA HOLE	A	206306-8
	SMALL PACK	NO	3.81 [.150] DIA HOLE	A	206306-6
	STANDARD	NO	4-40 THREADED INSERT	A	206306-5
	STANDARD	YES	-	B	206306-4
	STANDARD	YES	3.81 [.150] DIA HOLE	A	206306-3
	STANDARD	NO	-	B	206306-2
	STANDARD	NO	3.81 [.150] DIA HOLE	A	206306-1
	PACKAGING	PERIPHERAL SEAL	C	SEE DETAIL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.GELTZ CHK R.STONE APVD A.FRANTUM	07/26/93 08/11/93 08/13/93	NAME RECEPTACLE HOUSING, REVERSE SEX, SHELL SIZE 23, CPC -	
DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC 108-10024	APPLICATION SPEC	SIZE A1
MATERIAL HOUSING: NYLON, BLACK INSERT: BRASS	FINISH -	WEIGHT -	00779	DRAWING NO 206306	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1	REV N