





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AF	50		P	REVISED PER ECR-13-004343	30JUL13	KH
						APVD
						KR

- 1 FITS 0.81±0.025 X 4.75 [.032±.001 X .187] TAB
- 2 WIRE SIZE: 0.3–0.9mm² [22–18 AWG], STRANDED ONLY.
STRIP LENGTH 7.14 [.281]
- 3 INSULATION SIZE: 4.19 [.165] MAX DIA.
- 4 CONTINUOUS STRIP



BULK	TYPE 6/6 NYLON	RED TRANSLUCENT	BRASS	TIN	5–520336–2
		BLACK			9–520336–2
		RED TRANSLUCENT			2–520336–2
PACKAGING	MATERIAL	COLOR	MATERIAL	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN P FORTNEY 8/6/90		 TE Connectivity		
DIMENSIONS: mm [INCHES]			CHK MS FEHER 8/9/90				
			APVD D BRATINA 8/17/90		NAME RECEPTACLE ASSEMBLY,ULTRA-FAST FLAG, 4.75 [.187] SERIES		
			PRODUCT SPEC 108-2043				
			APPLICATION SPEC 114-2123				
			WEIGHT —				
TOLERANCES UNLESS OTHERWISE SPECIFIED:			0 PLC ± — 1 PLC ± — 2 PLC ± 0.38 [.015] 3 PLC ± — 4 PLC ± — ANGLES ± —		SIZE CAGE CODE DRAWING NO RESTRICTED TO		
MATERIAL SEE TABLE			FINISH SEE TABLE		A2 00779 C=520336 SCALE 8:1 SHEET 1 of 1 REV P		
CUSTOMER DRAWING							