




▲ CIRCUIT: SPST



NOTES:

1. ALL DIMENSIONS IN MM [INCH]

2. GENERAL TOLERANCE: x.x = ± 0.4 x.xx = ± 0.25

3. TERM. NOS. FOR REF ONLY

4. RATING: 50 MILLI-AMPS @24VDC

5. TRAVEL: 1.0 +/-0.5mm

6. CONTACT RESISTANCE: 30 MILLIOHMS MAX

7. INSULATION RESISTANCE: 10M OHMS MIN. AT 100VDC

8. DIELECTRIC STRENGTH: 250VAC FOR 1 MINUTE


▲ 9. OPERATING FORCE: 300 $\pm$ 75 GF

10. PACKAGING: TAPE AND REEL, 650 PIECES PER REEL

11. LIFE CYCLES: 10,000,000 ACTUATIONS

12. ▲ DENOTES CRITICAL PARAMETER

13. 2002/95/EC (ROHS) COMPLIANT



TITLE TL6200XBF300QG

A	21031	New Release	2/12/13	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE
2:1DATE
1/7/2013DR
rcDWG
T060100REV
A