



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C3	REVISED PER ECN-22-150900	27APR2022	RK	CSD




AMP WIRE RANGE	E13288 Listed
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED

LR7189 Certified
16-14 AWG SOLID OR STRANDED

- 1 STAMP AMP 16-14* APPROX AS SHOWN
- 2 UL 486 A-B

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C[338°F] MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
		WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm ² [2,050-5,180] CIR MILS SOLID OR STRANDED
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.
FOR ORDER ENTRY	1-800-526-5142	

		5000		ON TAPE		2-321684-1									
		1000		LOOSE PIECE		321684									
		QUANTITY		PACKAGING TYPE		PART NO									
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-17-93		 TE Connectivity											
		CHK DA PATTERSON 3-17-93													
DIMENSIONS: mm [INCHES]		APVD DE MILLER 3-17-93		NAME TERMINAL, RING TONGUE, SOLISTRAND™ —											
		PRODUCT SPEC 													
		APPLICATION SPEC —		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO					
MATERIAL COPPER PER ASTM B-152 ANNEALED		FINISH TIN PLATE 0.00254[.000100] MIN THK PER ASTM B-545		WEIGHT —		A2		00779		C-321684					
CUSTOMER DRAWING				SCALE		10:1		SHEET		1 OF 1		REV		C3	