

4

3


2

1


THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
© COPYRIGHT - By -		ALL RIGHTS RESERVED.	
PROJECT	PRJ-16-000909157		
PART NO.	X-2308345-X		
DESCRIPTION	FULL METAL HOODS SIZE 4		
CUSTOMER	GENERAL MARKET		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECR-16-013123	19SEP2016	KK	GG


1-2308345-3



1-2308345-7



Case



NOTES:

- FINISH:
1-2308345-1 TO 1-2308345-8 - CASE RAW
1-2308345-9 TO 2-2308345-6 - CASE NICKEL-PLATED
- LOCKING SCREWS: NICKEL-PLATED
OTHER SCREWS: ZINC-PLATED
- TEMPERATURE RANGE: -40°C TO +90°C
- CABLE DIAMETER WITH EXTERNAL DIAMETER CABLE CLAMP: 8-16 mm.
- STRAND DIAMETER OF CRIMP FLANGE: 3.7-10.7 mm.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KIRAN K 29JUL2016	 TE Connectivity			
DIMENSIONS: mm		CHK GUNASEKHAR G 29JUL2016				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN ISO 2768-m DIN 16901 130B	APVD GUNASEKHAR G 29JUL2016	NAME FULL METAL HOODS SIZE 4			
	0 PLC ± —	PRODUCT SPEC —	SIZE A2	CAGE CODE 00779	DRAWING NO C=2308345	RESTRICTED TO —
	1 PLC ± —	APPLICATION SPEC —				
	2 PLC ± —	—				
	3 PLC ± —	—				
4 PLC ± —	—					
MATERIAL —	FINISH —	WEIGHT				
CUSTOMER DRAWING			SCALE NTS	SHEET 1 of 2	REV A1	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

1-2308345-8	FULL METAL HOODS SIZE4-8	1-2308334-6	1-2308334-4	LOCKING SCREW (M3 LONG KNURLED)	LOCKING SCREW (M3 SHORT KNURLED)	S OVER	M3	98
1-2308345-7	FULL METAL HOODS SIZE4-7	1-2308334-5	1-2308334-3	LOCKING SCREW (4-40 UNC LONG KNURLED)	LOCKING SCREW (4-40 UNC SHORT KNURLED)		4-40 UNC	98
1-2308345-6	FULL METAL HOODS SIZE4-6	1-2308334-6		LOCKING SCREW (M3 LONG KNURLED)		50.0	M3	102
1-2308345-5	FULL METAL HOODS SIZE4-5	1-2308334-5		LOCKING SCREW (4-40 UNC LONG KNURLED)		50.0	4-40 UNC	102
1-2308345-4	FULL METAL HOODS SIZE4-4	1-2308334-4		LOCKING SCREW (M3 SHORT KNURLED)		24.0	M3	94
1-2308345-3	FULL METAL HOODS SIZE4-3	1-2308334-3		LOCKING SCREW (4-40 UNC SHORT KNURLED)		24.0	4-40 UNC	94
1-2308345-2	FULL METAL HOODS SIZE4-2	1-2308334-2		LOCKING SCREW (M3 W/SPRING WASHER)		20.7	M3	93
1-2308345-1	FULL METAL HOODS SIZE4-1	1-2308334-1		LOCKING SCREW (4-40 UNC W/SPRING WASHER)		20.7	4-40 UNC	93
PART NO.	DESCRIPTION	SUB-PART NO.		DESCRIPTION		A	d	WEIGHT, g
PART NO. (CASE RAW)		LOCKING SCREWS						


2-2308345-6	FULL METAL HOODS SIZE4-16	1-2308334-6	1-2308334-4	LOCKING SCREW (M3 LONG KNURLED)	LOCKING SCREW (M3 SHORT KNURLED)	S OVER	M3	98
2-2308345-5	FULL METAL HOODS SIZE4-15	1-2308334-5	1-2308334-3	LOCKING SCREW (4-40 UNC LONG KNURLED)	LOCKING SCREW (4-40 UNC SHORT KNURLED)		4-40 UNC	98
2-2308345-4	FULL METAL HOODS SIZE4-14	1-2308334-6		LOCKING SCREW (M3 LONG KNURLED)		50.0	M3	102
2-2308345-3	FULL METAL HOODS SIZE4-13	1-2308334-5		LOCKING SCREW (4-40 UNC LONG KNURLED)		50.0	4-40 UNC	102
2-2308345-2	FULL METAL HOODS SIZE4-12	1-2308334-4		LOCKING SCREW (M3 SHORT KNURLED)		24.0	M3	94
2-2308345-1	FULL METAL HOODS SIZE4-11	1-2308334-3		LOCKING SCREW (4-40 UNC SHORT KNURLED)		24.0	4-40 UNC	94
2-2308345-0	FULL METAL HOODS SIZE4-10	1-2308334-2		LOCKING SCREW (M3 W/SPRING WASHER)		20.7	M3	93
1-2308345-9	FULL METAL HOODS SIZE4-9	1-2308334-1		LOCKING SCREW (4-40 UNC W/SPRING WASHER)		20.7	4-40 UNC	93
PART NO.	DESCRIPTION	SUB-PART NO.		DESCRIPTION		A	d	WEIGHT, g
PART NO. (CASE Ni-PLATED)		LOCKING SCREWS						

NOTE:

* CRIMP FLANGE PN *-2308349-* TO BE ORDERED SEPARATELY.

* CRIMP BARREL TO BE USED IN COMBINATION WITH THE FLANGE PN *-2308350-* TO BE ORDERED SEPARATELY.

* CABLE CLAMP SCREW VERSION PN *-2308272-* TO BE ORDERED SEPARATELY.



CRIMP FLANGE




CRIMP BARREL



CABLE CLAMP

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:
DIN ISO 2768-m
DIN 16901 130B

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN KIRAN K 29JUL2016

CHK GUNASEKHAR G 29JUL2016

APVD GUNASEKHAR G 29JUL2016

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME

FULL METAL HOODS SIZE 4

SIZE A2

CAGE CODE 00779

DRAWING NO G=2308345

RESTRICTED TO -

SCALE NTS

SHEET 2 of 2

REV A1

1471-9 (1/15)

2308345