

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED(ECR-13-012673)	05.SEP.'13	CJ	HG
	A2	REVISED(ECR-20-011452)	13.AUG.'20	JH	GC








TABLE 1. APPLICABLE REC. CONTACT.

REC.	PART NO.	WIRE RANGE(mm ²)	INSULATION DIA.(mm) (FLR)
MQS (0.64)	1355717	0.14-0.22	0.9-1.2
	928999	0.2-0.5	0.9-1.6
	963715	0.5-0.75	1.6-1.9
MCP 2.8	A2 1564982	0.2-0.35	1.1-1.4
	1241388	0.5-1.0	1.4-2.1
	1241390	1.0-2.5	2.2-3.0
	968853	2.5-4.0	3.0-3.7



ISO VIEW



NOTE ;

- GENERAL TOLERANCE : ± 0.3 , $\pm 3.0^\circ$
- APPLICABLE REC. CONTACT : SEE TABLE 1.
- THE MATING CAP ASS'Y P/N : 1897540
- DELIVERY CONDITION : TPA 1'ST LOCKING.
- CURCUIT NO.
- MATERIAL ID MARK
- 1897543-2 : >PBT-GF15<
- 1897543-1 : >PA66-GF10<
- APPLICATION
- 1897543-2 : FOR IN-LINE CONNECTOR
- 1897543-1 : FOR TRANSMISSION CONNECTOR

2	1897545-6	PLUG DBL	PA66-GF10	RED	I	
	1897545-1		PBT	WHITE		I
1	1897544-1	PLUG HSG	PA66-GF10	NATURAL	I	
	1897544-2		PBT-GF15	BLACK		I
NO.	PART NO.	DESCRIPTION	MATERIAL	COLOR	Q'TY	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

-

FINISH

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC $\pm$

1 PLC ± 0.1

2 PLC ± 0.01

3 PLC ± 0.001

4 PLC ± 0.0001

ANGLES $\pm$

WEIGHT

-

CUSTOMER DRAWING

SCALE 2:1

DWN CJ CHOI

CHK KT LIM

APVD HG CHO

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

TE Connectivity

HYB(MQS/MCP2.8)22P PLUG HSG ASS'Y

A300779

1897543

1 OF 1

REV A2