

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

By

LOC

DIST

AJ

16

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

S2

REVISED PER ECO-12-008922

06SEP12

MGM

WM

1 . SEE I.S. SHEET 2028-1

3

2

1

21.01 MAX DIA

[.827]

A

MAX

4.78

[.188]

17.48 REF

[.688]

12.70

[.500]

9.53

[.375]

VIEW X

4.78

[.188]

17.48 REF

[.688]

12.70

[.500]

VIEW Y

RECOMMENDED STRIP LENGTH

		TBD	47.22 [.1859]	Y	BXS 7004-501	7-225092-6 AMP	225612-2	51695-2	225081-7	7-225092-6
OBSOLETE	220015-1	37.08 [1.460]	X		TIME AA-5888	7-2250902-5 AMP	225560-3	2-51695-2	225901-3	7-225092-5
OBSOLETE	220015-1	46.02 [1.812]	X		TIME AA-5886	7-225092-4 AMP	1-331987-0	1-51695-2	225081-1	7-225092-4
OBSOLETE	220015-1	46.81 [1.843]	X		TIME AA-5887	7-225092-3 AMP	225612-2	4-51695-0	225081-6	7-225092-3
SUPERSEDED BY 225092-2	-	-	-	-	-	-	-	-	-	7-225092-2
SUPERSEDED BY 225092-1	-	-	-	-	-	-	-	-	-	7-225092-1
OBSOLETE	-	-	-	-	-	-	-	-	-	1-225092-7
OBSOLETE	-	-	-	-	-	-	-	-	-	1-225092-6
OBSOLETE	-	-	-	-	-	-	-	-	-	1-225092-5
OBSOLETE	220015-1	47.22 [1.859]	Y		RG-214/U	10688470 AMP	331987	51695-2	225081-1	1-225092-2
	220015-1	47.22 [1.859]	Y		RG-393/U	1-225092-1 AMP	9-225490-1	2-51695-3	225081-1	1-225092-1
	220015-3	46.43 [1.828]	X		MICRODOT 250-4172, 250-4208	1-225092-0 AMP	225612-2	2-51695-1	225901-1	1-225092-0
	220015-3	46.43 [1.828]	X		MICRODOT 250-4171, 250-4207	225092-9 AMP	225612-1	2-51695-1	225901-2	225092-9
SUPERSEDED BY 414160-3	220015-1	47.22 [1.859]	Y		RG-115A/U	225092-8 AMP	1-331987-3	2-51695-1	225081-2	225092-8
	220015-1	47.22 [1.859]	Y		RG-225/U	00779M39012/01B0012 AMP & DATE CODE (YY-WW)	331987	51695-8	225081-1	225092-7
OBSOLETE	-	-	-	-	-	-	-	-	-	225092-6
OBSOLETE	-	-	-	-	-	-	-	-	-	225092-5
OBSOLETE	-	-	-	-	-	-	-	-	-	225092-4
	220015-1	47.22 [1.859]	X		RG-213/U	00779M39012/01B0007 AMP & DATE CODE (YY-WW)	1-331987-3	51695-2	225081-1	225092-2
	220015-1	47.22 [1.859]	Y		RG-214/U	00779M39012/01B0008 AMP & DATE CODE (YY-WW)	331987	51695-2	225081-1	225092-1
	CRIMP TOOL	A MAX	STRIP LENGTH VIEW		CABLE SIZE	STAMPING	③ FERRULE QTY=1	② CONTACT QTY=1	① PLUG ASSY QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:MM(INCHES)

0 PLC

±

-

1 PLC

±

-

2 PLC

±

-

3 PLC

±

0.41 [.016]

4 PLC

±

-

ANGLES

±

-

MATERIAL

-

FINISH

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

PRODUCT SPEC

108-12019

APPLICATION SPEC

-

WEIGHT

-

2-22-91

2-22-91

2-22-91

CUSTOMER DRAWING

DWN

M. SNEED

CHK

R. HENRY

APVD

R. HENRY

NAME

PLUG,WEATHERPROOF,SERIES N

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

SCALE

2:1

SHEET

1

OF

1

REV

S2

4805 (3/11)