

5

4

3

2


1

D



C

B

A



Minimum cable diameter: 3
Maximum cable diameter:
- with rubber bushing: 6,5
- without rubber bushing: 9,5



				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, 9 poles, top entry, straight metal hood with threaded inserts, for cable to cable application with latching	Maßstab/ Scale 1,5:1
			Detail.	27/06/08	PK			
			Insp.					
			Stand.					
09 67 009 0323	M3		35063	27/06/08	PK		TB 09 67 009 032X	Blatt/ Page 1 / 1
09 67 009 0322	4-40 UNC							
Part number	Threaded insert		Mod.	Dat.	Name			
			HARTING EURL F-95972 Paris				Sub.	