

5

4

3

2





1

D



C

B


A




Cable diameter



Cable diameters



Cable diameters



Scale: 2:1

Maximum cable outer diameter without grommet: 11,5 mm

				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, top entry hood with knurled screws, 9 poles, thermoplastic metallized	Maßstab/ Scale	
			Detail.	08/06/11	SD			1:1	
			Insp.	08/06/11	JB			2:1	
			Stand.						
			HARTING EURL F-95972 Paris					TB 09 67 009 0427	Blatt/ Page 1 / 1
EC03320	08/06/11	SD							
Mod.	Dat.	Name							



All Dim. in mm
Orig. Size DIN A 4

D-Sub, top entry hood
with knurled screws,
9 poles,
thermoplastic metallized

Maßstab/
Scale

1:1
2:1

Blatt/ Page

1
1